R 9600

Generation 8

LIEBHERR

Mining excavator



- Cutting-edge technologies

- Advanced machine monitoring

3,620 HP

Cummins: 2,500 kW (FCO, Tier 4f)

3,350 HP

Electric: 2,400 kW (50 Hz, 60 Hz)

3,220 HP

698 tons

Bucket payload: 68 tonnes

75 tons

711 tons

Bucket payload: 67 tonnes

74 tons



Weight-optimised attachment

The R 9600 attachment makes use of smart component design such as the patented "EVO" backhoe bucket, hydraulic cylinders, shift levers, bucket links and attachment pins. The result is an increased overall production rate without compromising component lifetime.

Standard heavy-duty bucket

- Highest bucket capacity in its class with proven EVO bucket design.
- Maximised payload with versatile Liebherr Bucket Solution.
- Shift levers and bucket links with integrated greasing system.

Perfect shovel truck match

3 pass loading of 190 tonne trucks 4 pass loading of 240 tonne trucks 5 pass loading of 290 tonne trucks 6 pass loading of 375 tonne trucks



Latest cabin generation

Increased comfort and ergonomics


- User-friendly operator station
- Suspended operator & trainer seats
- Slim line dash and ambient lighting
- Refrigerator and optional vacuum cleaner

Latest cutting-edge technologies

- Liebherr Assistance Systems
- Advanced machine monitoring with modern 7" and 15" touchscreens (day & night mode)
- 270° vision system with large dedicated 15" monitor

Sustainable performance

- US EPA Tier 4f/EU Stage V compliant engine
- SCR after-treatment technology
- Serial implementation of Liebherr Power Efficiency solutions
- Electric Drive version





Diesel drives

The R 9600 can be fitted with two versions of diesel drive systems. Customers can choose between the Liebherr D9812 and the Cummins QSK50 engine, both providing superior performance for increased productivity.

Liebherr 2x D9812

2,700 kW / 3,620 HP at 1,800 RPM 12 cylinder V-engine Displacement 62.04 l / 3,785.9 in3

Cummins 2x QSK50

2,500 kW / 3,350 HP at 1,800 RPM 16 cylinder V-engine Displacement 50.3 l / 3,067 in³

US EPA Tier 4f/EU Stage V

Both engines use selective Catalytic Reduction technology to comply with latest emission regulations the R 9600 combines flexibility to meet customer expectations without compromising productivity.





Electric drive

Liebherr offers an alternative to diesel engines allowing customers to balance performance with environmental consciousness. Building on 30 years' experience in electric drive excavators, the electric drive option allows lower maintenance costs and reduced noise pollution. With high motor efficiency, the electric drive gives maximum performance.

- Lower maintenance costs
- 6,000 V (other voltage on request)
- Integrated design elements on all machine structures
- Optional cable reeler

No exhaust emission

Liebherr electric R 9600 provides class leading cycle times using electric motors without exposing people and the environment to diesel exhaust emissions. Complying with all Non Road Mobile Machinery (NRMM) emission regulations, the R 9600 E can be operated all around the world.

Less noise level

Liebherr Electric driven machines can be operated without restrictions in noise sensitive areas.



Productivity

Attachment

Setting new standards in the mining industry



Backhoe

37.5 m³

49.1 yd3



6 Pass



5 Pass



240t Trucks 4 Pass



3 Pass



Face Shovel

37.0 m³

48.4 yd3



290t Trucks

6 Pass

240t Trucks 5 Pass

190t Trucks

4 Pass




The optimised design of the R 9600 attachment increases the overall productivity without compromising component lifetime.

Maximised payload

Designed for best force distribution, the attachment design delivers high digging and hoisting forces, which ensures maximum payload during each cycle. The EVO bucket allows the operator to take advantage of each pass and therefore increase productivity.

Optimised cost per tonne

Built to outperform all competitors in the 600t class, the R 9600 offers superior durability through its brand new machine and component design, delivering state-of-theart capabilities and reliability.





Automation

Bucket Filling Assistant


The first automation product of the Liebherr hydraulic excavator portfolio allows easier bucket filling and consistent bucket fill factors, especially in blocky or hard digging conditions. As a result overall productivity improves while operator's fatigue decreases.



Anti-Stalling Function
Prevents the bucket from being stalled during the digging phase.



Semi-Automatic Bucket Filling FunctionAllows the machine electronic to realise fully automatic attachment movements.






Latest cabin generation

- Spacious interior
- Modern and large touchscreens
- Indirect ambiance LED lights
- Drawer refrigerator
- User-friendly piloting station
- Best in class visibility




Superior comfort

- Only 69 dB noise level
- Suspended and heated seats
- Synthetic leather interior
- Pressurised A/C system (single or double)
- Reading spotlights with tablet
- Phone and cup holders



360° vision

The R 9600 offers superior visibility of the machine's surroundings. The dedicated monitor inside the cabin provides continuous 270 degree vision around the machine, from the four cameras strategically fixed on the uppercarriage. The operator has 90 degrees of direct visibility in front of the cabin.



Working environment

Operator comfort

Resiliently mounted, the cab design reduces vibrations and limits noise to provide a comfortable workspace. Standard ambient lighting ensures even at night a serene working environment.

Perfect working position

The slim line dash allows positioning of operator's seat as far left as possible providing best visibility of the working area.

Additional features

Dedicated mounting points for additional customer devices, modules or antennas.

First class cabin

Operator and trainer seats are air-suspended and heated offering a high level of comfort. Beyond these outstanding features, Liebherr offers as standard a 20 litre drawer refrigerator and an optional vacuum cleaner fitted directly into the cabin.

Optional

- Double A/C system
- Vacuum cleaner
- Premium cooled seats
- Four point harness
- HEPA filtration system

Assistance Systems The Best Performance. Easy.

Get the best out of your Liebherr Mining Excavator

Available today on the R 9600, the Liebherr Assistance Systems are advanced onboard applications designed to support operators to become more efficient through analytics and actionable insights. Systems will assist the operator to obtain optimal productivity and efficiency by providing realtime operational information.



Want to live the real experience?



Measure and analyse every bucket payload for optimal truck loading



Data visualised within different views & advanced filtering



Display targeted productivity and actual payload with 99% accuracy



Provide transparency of performance, operating time and fuel efficiency



Identify operational conformance and improve operator effectiveness




State-of-the-art on board touchscreen displays



Make informed decisions



Increase productivity





Truck Loading Assistant

Assists the operator to obtain target truck payloads.

With 99% measurement accuracy

- Measures instantaneously the bucket payload
- Provides real-time information to the operator
- Strategises the number of passes required
- Computes the best truck loading strategy
- Automatic truck recognition (optional)



Application Severity

Quantifies application, reports severity indicators and provides an overall application severity score.

KPIs to indicate and display the application as sensed by the machine

- Underfoot and digging conditions
- Abrasiveness and travel ratio
- Engine load factor and temperature variation
- Machine inclination, loading, etc.



Performance Monitoring

Measures and analyses the overall performance.

Using KPIs, histograms and time-related charts

- Production KPIs
- Loading indicators
- Time distribution
- Energy efficiency



Operational Conformance

Detects and counts events to improve operator effectiveness.

Several filtering criteria to identify specific events

- Swinging into digging face
- Digging with swing brake activated
- Turning the machine with the attachment
- Bucket hitting track pads, etc.



Fast & precise movement

Intelligent power management system

The Liebherr R 9600 mining excavator is equipped with a closed loop swing circuit. Kinetic energy is recovered when the swing motion is used during deceleration to drive the main and auxiliary pumps. This reduces fuel consumption and supports faster boom lift speed. Cylinder dampening through IMUs provides smoother attachment movements without affecting attachment speed.

Independent cooling system

Oil and water cooling fans are independently and electronically managed. The oversized cooling systems reduce parasitic demand on engine horsepower ensuring maximum available horsepower is provided to the excavator working circuits.

New valve bank control system


- Under slung arch hoses to improve lifetime
- Flow optimized hose fittings
- Less hydraulic pressure losses by design
- Pilot valves integrated into valve blocks

Moving more with less


Liebherr Power Efficiency

Specific engine and hydraulic management, drastically reducing fuel consumption.

- Adapted piloting processes according to operator requirements and machine condition
- Electronically controlled pressure and oil flow
- Reduce hydraulic throttling and load profile of the engine for increased component lifetime



Up to 20% less fuel consumption




"Adapt the power and the hydraulic flow specifically to the load profile."





Safe machine accessibility

The R 9600 is fitted with an ergonomic hydraulically controlled 45 degree stairway with handrails, providing safe access to the uppercarriage.



Wide catwalks for inspection

Enlarged walkways allow easy and safe access for inspection and maintenance around engines, fans, and pumps. All routine service items have been located to allow effortless inspection and replacement.



Emergency stops and emergency exits


Emergency Stops are specifically located throughout the machine, increasing safety. A mechanical emergency egress with handrails guaranties safe and quick exit from the machine. An additional emergency drop down ladder is provided in the pump bay.





Advanced engine fire protection

After treatment systems and turbochargers are heat shielded. The engines are mechanically segregated from hydraulic components, further improving on machine safety.



LED lighting system

Thanks to 16 LED long-reach lights located on attachment, uppercarriage and counterweight, the machine offers best visibility to the operator but is also easily visible at night.



Safe surrounding area

The operator can manage the lighting system through several switches to guarantee safe 24/7 operation. Pneumatic horn system can be switched to light signal at night.

Easy & safe operations

Maintenance




Centralised service

Service flap

Uppercarriage of the R 9600 has been designed for easier maintenance and quicker servicing. The central service area provides accessibility to uppercarriage fluid compartments

reducing machine downtime. Refill and separate drain points of the R 9600 are easily accessed from the ground with fast couplings and depressurised valves.





Automatic greasing system

- 600 litre grease tank
- Simplified component layout
- Automatic greasing cycles
- SKF Power Contimaster pumps
- Reduced number of injectors & hoses
- Electric shut-off valve in the refill line



Superior engine accessibility

- Walkways all around the engines
- Service-friendly maintenance items installation
- Service interval 500 hours (Optional 1000 hours)
- Sampling-point for all liquids on deck



Ease of troubleshooting

- Signal panels
- Control system hardware and software completely developed and managed by Liebherr
- Reduced number of connections and connectors

Optional

- Service folding platform on front swing boxes
- Service doors on travel drive protection
- Additional Cummins oil reserve tank

- Banlaw or Wiggins couplings
- Kidney loop filtration system

Long-lasting performances Reliability

Vertical integration

As an OEM, Liebherr has built a solid reputation for its development and production of high quality strategic mining components. The R 9600 integrates robust and reliable mining optimised components that are developed and manufactured by Liebherr, which ensures the best reliability and highest performance.

Mining know-how

Liebherr mining excavators are conceptualised, designed and dedicated to the mining industry.


The engineering department uses specific 3D simulation solutions in order to meet possible requirements, such as finite element and fatigue life analysis.



Robust undercarriage

- Hydraulic track tensioning system
- Smart achitecture optimising hydraulic flow
- Final drive with double lifetime sealing in series
- Fatigue resistant steel structure design
- Sealed for life heavy-duty carrier and track rollers
- Patented track pad design





Super structure

- Complete new development
- Optimised welding penetration
- Increased structural rigidity and life



Quality: the Liebherr trademark

Providing reliable machinery is the highest priority for Liebherr Mining. Utilised in tough mining applications all around the world, our R 9600 is built to last over 80,000 operational hours. Liebherr's engineering expertise and continuous improvement programs combine to deliver industry leading machines.

The four pillars of the Liebherr mining division

With more than 50 years of experience in the mining industry, Liebherr has identified four key factors of customer satisfaction: Performance, Safety, Service, and Sustainability. These pillars provide structure and focus for all our activities, and embody Liebherr's customer commitments.





Performance

Productive, efficient and reliable



Safety

Protecting your most important assets




Service

Where you need it, When you need it



Sustainability

Committed to our future



Technical data

Powertrain

2 Liebherr diesel engines	
Rating ECE-R.24/ ISO 9249	$2\times1,\!350$ kW / $2\times1,\!810$ HP at 1,500 rpm
Model	Liebherr D9812 (Fuel Consumption Optimized setting or US EPA Tier 4f / EU Stage V)
Туре	12 cylinder V-engine
Bore / Stroke	175 / 215 mm / 6.89 / 8.46 in
Displacement	62.04 l / 3,786 in³
Engine cooling system	fans driven via hydraulic piston motors
Liebherr Power Efficiency - Engine Control	engine management systems adapting the power specifically to the load profile
Air cleaner	dry-type air cleaner with pre-cleaner, with automatic dust ejector, primary and safety elements
Fuel tank	14,067 l / 3,716 gal
Fuel filtration	3 Stage fuel filtration with water separator and electric priming pump
Oil lubrication	spin-on filters and oil centrifuge filter
Electrical system	
Voltage	24 V
Batteries	8 x 180 Ah / 12 V starting battery 4 x 180 Ah / 12 V service systems
Alternator	24 V / 370 Amp
Engine idling	automatic engine idling
or	
2 Cummine discal and	inge

2 Cum	nmins diesel eng	ines
Rating	per SAE J1995	2 x 1,250 kW / 2 x 1,675 HP at 1,800 rpm
Model	l	Cummins QSK50 (Fuel Consumption Optimized setting or US EPA Tier 2 or US EPA Tier 4f / EU Stage V)
Type		16 cylinder V-engine
Bore /	/ Stroke	159 / 159 mm / 6.26 / 6.26 in
Displa	acement	50.3 l / 3,067 in ³
Engine	e cooling system	fans driven via hydraulic piston motors
Efficie	err Power ency ne Control	engine management systems adapting the power specifically to the load profile
Air cle	eaner	dry-type air cleaner with pre-cleaner, with automatic dust ejector, primary and safety elements
Fuel to	ank	14,067 l / 3,716 gal
Fuel f	iltration	2 Stage fuel filtration with water separator and electric priming pump
Oil lub	orication	spin-on filters (4x)
Electr	rical system	
Voltag	ge	24 V
Batte	ries	8 x 180 Ah / 12 V starting battery 4 x 180 Ah / 12 V service systems
Altern	ator	24 V / 260 Amp
Engin	e idling	automatic engine idling

Lingine lutting	automatic engine lumg
or	
2 electric motor	
Power output	2 x 1,200 kW / 2 x 1,610 HP
Туре	3-phase AC squirrel cage motor
Voltage	6,000 V (other voltage on request)
Frequency	50 Hz (or 60 Hz)
Revolutions	1,500 rpm (or 1,800 rpm)
Motor cooling	integrated air-to-air exchanger
Starting method	inrush current limited to 2.2 full load current
Starting sequence	successive startup of electric motors

Electro-hydraulic controls

Servo circuit	independent, electronic over hydraulic proportional controls of each functions
Emergency control	emergency lowering of the attachment to the ground, via accumulators
Power distribution	via monoblock control valves with integrated primary relief valves, proportional and safety valves. Integrated secondary relief valves on functional blocks and motors
Electro-hydraulic servo control	
Attachment and swing	proportional via joystick levers
Travel	proportional via foot pedals
Electronic dampening system	Liebherr designed electronic control of cylinder position via inertial measurement units

Swing drive

Hydraulic motor	4 Liebherr axial piston motors
Swing gear	4 Liebherr planetary reduction gears
Swing ring	Liebherr, sealed triple roller swing ring, internal teeth
Swing speed	0 – 3.7 rpm
Swing-holding brake	4 hydraulically released, maintenance-free, external multi-disc brakes

Hydraulic system

, araano o, otom	
Hydraulic pump for attachment and travel drive	8 Liebherr variable flow axial piston pumps
Max. flow	8 x 800 l/min. / 8 x 211 gpm
Max. pressure	320 bar / 4,641 psi
for swing drive	4 Liebherr reversible swashplate pumps, closed-loop circuit
Max. flow	4 x 530 l/min. / 4 x 140 gpm
Max. pressure	320 bar / 4,641 psi
Pump management	electronically controlled pressure and flow management with oil flow optimisation
Hydraulic tank capacity	5,425 l / 1,433 gal
Hydraulic system capacity	9,600 l / 2,536 gal
Hydraulic oil filter	1 high pressure safety filter after each main pump + fine filtration of the entire return flow (15 / 5 μm) dedicated leak-oil filtration
Hydraulic oil cooler	4 separated coolers with 3 temperature controlled fans driven via hydraulic piston motors
Liebherr Power Efficiency - Hydraulic Control	hydraulic management system adapting the hydraulic flow specifically to the load profile

Electric system

	Electric isolation	easily accessible battery isolations (single isolation point)
	Working lights	LED lights arrangement around the attachment and the uppercarriage
	Emergency stop switches	at ground level, in engine and pumps compartment, at valve bank and in operator cab
	Electrical wiring	heavy duty execution in IP 65 standard for operat- ing conditions of -55°C to 135°C / -67°F to 275°F

Uppercarriage

Design	torsion resistant designed upper frame in box-type construction for superior strength and durability
Attachment mounting	parallel longitudinal main girders in box section construction
Machine access	45° access system with handrails on the cab side of the uppercarriage, full controlled descent in case of emergency stop. Emergency egress fitted near the cab and emergency ladder in the pump bay.

Operator's cab

uperator's cap	
Design	resiliently mounted, sound insulated, large windows for all around visibility, integrated falling object protection (ISO 10262)
Operator's seat	suspended pneumatic seat, body-contoured with shock absorber, adjustable to operator's weight, additional suspended pneumatic passenger / trainer seat, seat heating
Cabin windows	tinted armored glass for front window and right- hand side window P5A (EN 356), all other safety windows tinted, high pressure windshield-washer system with 75 l / 20 gal watertank, sun louvers on all windows in heavy duty design
Heating system / Air conditioning	heavy duty, fully automatic, "plug & play" system, high output air conditioner and heater unit, contains fluori-nated greenhouse gases HFC 134a with a Global Warming Potential (GWP) of 1430, the AC circuit con-tains 4.1 kg / 9 lb of HFCa-134 representing an equiva-lent of 5.9 tonnes/ 6.5 tons of CO2, the second AC cir-cuit (optional) contains 4.1 kg / 9 lb of HFCa-134 repre-senting an equivalent of 5.9 tonnes / 6.5 tons of CO2
Cabin pressurisation	ventilation with filters, minimum pressurisation of 50 Pa (ISO 10263-4)
Controls	joystick levers integrated into armrest of seat, armrest adjusted to seat position
Display	15" machine touch panel for machine control and Liebherr Assistance Systems, 7" auxilliary touch panel for auxiliary/comfort control, 15" camera display
Condition monitoring	machine condition monitoring system with error reporting and operational information
Vision system	4 cameras providing 270° view
Safety functions	Automatic engine shut off safety mode for engine speed control and pumps regulation
Noise level (ISO 639	Diesel LpA (inside cab) = 69 dB(A) Electric LpA (inside cab) = <69 dB(A)
Hand-arm vibrations	≤ 2,5 m/s2
Whole-body vibrations	≤ 0,5 m/s2

Undercarriage

Design	3-piece undercarriage, box-type structure for center piece and side frames, stress relieved
Hydraulic motor	2 axial piston motors per side frame
Travel gear	Liebherr planetary reduction gear
Travel speed	Diesel : 0 - 1.7 - 2.2 km/h / 0 - 0.6 - 1.2 mph
Parking brake	spring engaged, hydraulically pressure released external wet multi-disc brakes for each travel motor, maintenance-free
Track chain	dual pin monobloc casted pads, maintenance free
Track rollers / Carrier rollers	6/3 per side frame
Automatic track tensioner	pressurised hydraulic cylinder with accumulator, maintenance-free

Service flap

Design	hydraulically actuated service flap, easily accessible from ground level, including:
	- fast fuel refill line - hydraulic oil refill - engine oil exchange - splitterbox oil exchange - swing gearbox oil exchange (4x draining / 4x refill) - swing ring teeth grease barrel refillling with grease filter and shutoff valve when high level reached - attachment / swing ring bearing grease barrel refilling with grease filter and shut off valve when high level reached - connection for windshield washer water refilling - oil reserve system refilling (optional) - DEF exchange - coolant filling


Central lubrication system

Туре	single-line lubrication system for the entire attachment / swing ring bearing and teeth
Grease pumps	2 hydraulic grease pumps for attachment / swing ring bearing lubrication,1 hydraulic grease pump for swing ring teeth
Capacity	600 l / 158.5 gal bulk container for attachment / swing ring bearing, separated 80 l / 21 gal container for swing ring teeth
Refill	via the service flap
Monitoring	via a specific Liebherr control module with data memory

Attachment

Design	box-type structure with large steel castings in all high-stress areas
Stick	wear protection underneath lower beam plate
Pivots	two floating pins per pivot, sealed covers, all bearings with wear resistant steel bushings, bolts hardened and chromium-plated
Hydraulic cylinder	Liebherr design, electronically controlled end-cushioning
Hydraulic connections	pipes and hoses equipped with SAE connections
Pivots bucket-to-stick Pivots bucket-to-link	O-ring sealed and completely enclosed
Lubrication	connected to the centralised lubrication system, each lubrication point independently lubricated

Dimensions




	mm / ft in
Α	7,310 / 23'12"
Al	8,160 / 26'9"
A2	9,220 / 30'3"
В	7,870 / 25'10"
С	9,610 / 31'6"
D	7,950 / 26'1"

	mm / ft in
F	3,331 / 10'9"
G	8,175 / 26'10"
Н	6,760 / 22'2"
H2	8,290 / 27'2"
H3	9,980 / 32'74"
K	3,100 / 10'2"

	mm / ft in
L	7,850 / 25'9"
N	1,350 / 4'5"
Р	3,010 / 9'11"
Q	1,390 / 4'7"
S	6,330 / 20'9"
U	10,325 / 33'10"

	mm / ft in
V	15,210 / 49'11"
W	9,500 / 31'2"
W2	9,950 / 32'8"
X	21,950 / 72'
Z	13,100 / 42'12"
OEL (Operator's eye level)	8,360 / 27'5"



	mm / ft in
Α	7,310 / 23'12"
Al	8,160 / 26'9"
A2	9,220 / 30'3"
В	7,870 / 25'10"
С	9,610 / 31'6"
D	7,950 / 26'1"


	mm / ft in
F	3,331 / 10'9"
G	8,175 / 26'10"
Н	6,760 / 22'2"
H2	8,290 / 27'2"
Н3	9,980 / 32'74"
K	3,100 / 10'2"

	mm / ft in
L	7,850 / 25'9"
N	1,350 / 4'5"
Р	3,010 / 9'11"
Q	1,390 / 4'7"
S	6,330 / 20'9"
U	10,325 / 33'10"

	mm / ft in
V	18,400 / 60'4"
W	8,760 / 28'9"
Wl	9,500 / 31'2"
X	24,530 / 80'6"
Z	13,100 / 42'12"
OEL (Operator's eye level)	8,360 / 27'5"

Backhoe attachment

with Mono Boom 10.90 m / 35'9"



Digging envelope

Stick length	m ft in	5.00 16'5"
Max. digging depth	m ft in	8.10 26'7"
Max. reach at ground level	m ft in	19.20 62'12"
Max. dumping height	m ft in	10.60 34'9"
Max. teeth height	m ft in	16.20 53'2"

Forces

Max. digging force (ISO 6015)	kN lbf	1,575 354,074
Max. breakout force (ISO 6015)	kN lbf	1,740 391,168

Operating weight and ground pressure

The operating weight includes the basic machine with backhoe attachment and backhoe bucket 37.50 m³ / 49.05 yd³.		
Pad width	mm ft in	1,350 4'5"
Weight	kg lb	633,000 1,395,526
Ground pressure*	kg/cm²	2.69

^{*} according to ISO 16754

Backhoe buckets

For materials class according to VOB, Section C, DIN 18300		3 - 4	5 - 6	5 - 6	7 - 8
Typical operation according to VOB Section C, DIN 18300		GP	HD	HD	XHD
Capacity ISO 7451	m³	39.00	40.00	37.50	33.30
	yd³	51.01	52.32	49.05	43.56
Suitable for material up to a specific weight of	t/m³	1.8	1.65	1.8	2.05
	lb/yd³	3,035	2,782	3,035	3,457
Cutting width	mm	4,800	4,800	4,600	4,600
	ft in	15'8"	15'8"	15'1"	15'1"
Weight	kg	34,000	38,200	36,800	36,300
	Ib	74,957	84 216	81 130	80,028


GP: General purpose bucket HD: Heavy-duty bucket

XHD: Heavy-duty rock bucket

Other buckets for other densities and/or material classes on request

Face shovel attachment

with Shovel Boom 7.90 m / 25'11"



Face shovel buckets

For materials class according to VOB, Section C, DIN 18300		3 - 4	5 - 6	5 - 6	7 - 8
Typical operation according to VOB Section C, DIN 8300		GP	HD	HD	XHD
Capacity ISO 7451	m³	38.50	39.00	37.00	34.00
	yd³	50.36	51.01	48.40	44.47
Suitable for material up to a specific weight of	t/m³	1.8	1.65	1.8	2.00
	lb/yd³	3,035	2,782	3,035	3,373
Cutting width	mm	5,200	5,200	5,200	5,200
	ft in	17'0"	17'0"	17'0"	17'0"
Weight	kg	61,000	66,000	63,900	62,500
	lb	134,482	145,505	140,875	137,789

GP: General purpose bucket HD: Heavy-duty bucket XHD: Heavy-duty rock bucket

Other buckets for other densities and/or material classes on request

Digging envelope

Stick length	m ft in	5.10 16'9"
Max. reach at ground level	m ft in	15.90 52'2"
Max. dumping height	m ft in	12.40 40'8"
Max. crowd length	m ft in	4.80 15'9"
Max. teeth height	m ft in	19.50 63'12"
Bucket opening width T	m ft in	3.20 10'6"

Forces

Crowd force at ground level (ISO 6015)	kN lbf	2,425 545,162
Max. crowd force (ISO 6015)	kN lbf	2,625 590,124
Max. breakout force (ISO 6015)	kN lbf	2,125 477,719

Operating weight and ground pressure

The operating weight includes the basic machine with shovel attachment and bucket 37.00 m³ / 48.40 yd³.				
Pad width	mm ft in	1,350 4'5"		
Weight	kg lb	645,000 1,421,982		
Ground pressure*	kg/cm² psi	2.74 38.97		

^{*} according to ISO 16754

Optional equipment

Undercarriage

Large track pads

Center girder lower cover plate

Swing ring scrapers

Uppercarriage

Steel grease lines on swing ring

Rock protection for fuel tank

Rock protection for hydraulic tank

Wiggins or Banlaw fast refilling systems

Coolant draining/filling from service flap

Additional RHS catwalks for windshield access

Automated sampling point

Additional fast fuel refill line

Hydraulic system

Oil cooler inlet screens

Kidney loop filtration system

Additional catwalks inside hydraulic tank

Powertrain

Tier 2, Tier 4f engine versions

Cummins oil reserve system

Operator's cab

4-points seat belt

Premium cooled seats

Vacuum cleaner

Double A/C system

Front protective grid

Leatherette seats

Cabin pressurisation with HEPA filters

Automation

Bucket Filling Assistant

Specific solutions

Arctic package (-20 °C/-4°F, -35°C/-31°F, -50°C/-58°F)

Sound attenuation package (until +40°C/+104°F)

High altitude package

Oil sand package

Cable reeler (Electric Drive)

Safety

Automatic fire fighting system

MDG41 Compliant - Isolation & Energy dissipation system

Service folding platform over front swing boxes

Starter inhibition from ground level

Fall Restraint Cable on Boom (CE certified)

Fall Restraint Cable on Boom (AS/NZL certified)

General

Maritime transport packaging

Delivery without batteries



Quality commitment

- Liebherr-Mining Equipment Colmar, France, ISO 9001 certified
- Compliance of materials tested in laboratory
- Quality control during all stages of production