

Performance

Power plus speed – Redefined performance

Economy

Good investment – Savings for long-term

Reliability

Durability and sustainability – Quality down to the last detail

Comfort

Perfection at a glance – When technology is comfortable

Maintainability

Efficiency bonus –

Even with maintenance and service



LH 40 M Industry Litronic

Operating weight

80,200-85,300 lb * 1)

Engine

208 HP / 155 kW (Diesel) 145 kW (Electric)

Stage V

Stage IIIA (compliant) Tier 4 Final

Electric

System performance

237 kW (Diesel) 227 kW (Electric)

LH 40 C Industry Litronic

Operating weight

82,900-90,200 lb * 1)

Engine

208 HP / 155 kW (Diesel) 145 kW (Electric)

Stage V

Stage IIIA (compliant)

Tier 4 Final Electric

System performance

237 kW (Diesel) 227 kW (Electric)

^{*} Without attachment

¹⁾ Different operating weight with electric drive



LH 50 M Industry Litronic

Operating weight

88,200-95,900 lb*

Engine

208 HP/155 kW Stage V

Stage IIIA (compliant) Tier 4 Final

System performance

269 kW

LH 50 M High Rise Industry Litronic

Operating weight

102,300-103,400 lb *

Engine

208 HP/155 kW

Stage V

Stage IIIA (compliant) Tier 4 Final

System performance

269 kW

LH 50 C High Rise Industry Litronic

Operating weight

117,500-121.000 lb*

Engine

208 HP/155 kW

Stage V


Stage IIIA (compliant)

Tier 4 Final

System performance

269 kW

Performance



Power plus speed – redefined performance

Liebherr has been designing and manufacturing market leading machines for material handling machines for over 60 years. The generation of Liebherr handlers, the LH 40 and LH 50, are high performance yet economical machines specially designed for use in scrap recycling, in timber yards and also for bulk handling.

Maximum handling capacity

High engine output

Due to the high engine power, the system has a hightorque for more powerful, faster movements. Furthermore, the machine automatically compensates for load peaks, meaning full torque is available at all times for maximum handling capacity.

High swing torque

The separate hydraulic pump in the closed slewing circuit only supplies hydraulic fluid to the swing mechanism. The maximum delivery volume is thus available at any time for turning the uppercarriage for fast and dynamic rotational movements.

Energy recovery system ERC

Lowering the equipment in the ERC system provides the machine with additional stored energy. This results in increased system performance, which in turn enables more powerful, faster and more homogeneous work cycles and increases handling performance.

Precision operation

LSC Hydraulic system with electrical pilot control

The 2-circuit Liebherr-Synchron-Comfort-system (LSC) with LUDV technology (flow distribution independent of load pressure) ensures faster working movements with up to 20% less energy consumption in comparison to the predecessor models.

All work functions of the machine are controlled electrically, whereby the signals of the transmitters are only converted directly at the control block by hydraulic means. This technology enables end position damping of the equipment in order to protect the components and thus extend their service life. Simple, individual setting and adjustment of the working speed of boom, stick and slewing mechanism allow the driver to adjust the machine to each application and fully utilize the machine's capacity.

Firm and stable positioning

An essential prerequisite for precise working and maximum handling capacity is the firm and stable positioning of the machine. The design of the Liebherr undercarriage optimizes the way forces are induced on components to minimize stress and guarantee maximum stability and durability.




Liebherr diesel engine compliant with Tier 4 Final

- Powerful, robust and reliable
- Maximum torque even at low speeds to ensure fast movements with low fuel consumption
- Common-Rail injection system for maximum efficiency
- Emissions treatment with Liebherr SCR technology



Closed slewing circuit

- High torque for maximum acceleration and fast rotary movements
- Integrated speed sensor for controlling and monitoring braking movement for greater safety
- Greater fuel efficiency thanks to intelligent energy management in the closed system



Electrical pilot control

- Precision control irrespective of the ambient temperature for maximum precision
- Simpler and faster fault diagnostics for optimal availability
- Up to 5 individual driver profiles can be saved

Economy



Good investment – savings for the long-term

Liebherr material handling machines combine high productivity with excellent economy thanks to the use of in-house components as well as sophisticated engine technology and highly efficient demand-controlled hydraulics.

Increased productivity

Engine idling and engine shut-down

The standard automatic idling function reduces the engine speed to idle as soon as the operator takes his hand from the joystick so that no hydraulic function is activated. Proximity sensors in the joystick levers restore the original engine speed as soon as the operator's hand is moved towards the lever again. This ensures that the set engine speed is available immediately. The result is a combination of energy saving and reduced noise levels. Operating costs can be reduced even further with the optional automatic engine shut-down function.

Closed hydraulic circuit for the swing mechanism

The closed slewing circuit feeds the braking energy back into the system when the uppercarriage is braked. Here, new standards are set in terms of efficiency and economy. Simple yet effective.

Attachments and quick coupling systems

Liebherr offers a wide selection of attachments for every application to increase the productivity of its material handling machines. In addition the material handlers can be fitted with a Liebherr quick coupling system which increase the productivity of the machine by up to 30%. The matching attachment and quick coupling system combined with the outstanding dynamics of a Liebherr handler ensures highest handling capacity and maximum productivity.


Electrical efficiency

Electric drive concept

The electric drives offer an economical and sustainable solution in the field of material handling. The drive motors operate in an environmentally friendly and emission-free manner, which makes them independent of any exhaust emission standards. A significant reduction in operating and service costs is achieved due to the elimination of maintenance work such as oil changes and fuelling breaks, as well as longer service intervals compared to diesel models. This increase in efficiency results in optimal working times and increased productivity in the field. In addition, the low-vibration and low-noise operation ensures improved working comfort.

Sustainable profitability with electric machines

An investment in an electric material handling machine pays off in the long term. These advanced drives offer numerous advantages that enable fast amortisation of the machine and significant cost savings compared to conventional diesel engines. Given the growing importance of environmental criteria and emissions, electric drives are an economical alternative that ensures both sustainable profitability and environmentally friendly operation.



Low energy consumption thanks to intelligent machine control

- Liebherr-Power Efficiency (LPE)
 optimizes the interaction of the drive components in terms of efficiency
- LPE enables machine operation in the area of the lowest specific energy use for less consumption and greater efficiency with the same performance



Liebherr-attachments

- Robust and service-friendly slewing drive, can be turned 360°
- Optimum filling and clamping performance for effective material handling
- Finite element method (FEM)
 optimized for a perfect relationship
 between grapple weight, volume and
 a very long service life




Frequency converters

- Individual adjustment of the speed
- Smooth start-up to avoid inrush current peaks and high energy savings due to effective start-up current limitation
- Simple adjustment to all conventional power supply networks

7

Reliability



Durability and sustainability – quality down to the last detail

Every day Liebherr material handlers demonstrate their qualities in a range of industrial applications all over the world. Years of experience, continuous development and the latest technologies provide maximum safety in use. Their robust design and the use of components produced in-house ensure that the LH 40 and LH 50 are designed for a long service life.

More safety

Pipe fracture safety valves

The standard pipe fracture safety valves on the stick and hoist cylinders prevent the equipment from dropping in an unregulated way and ensure maximum safety during every operation.

Working range limiters

For operations in which the working range should be limited, the material handling machines can be specified with an optional working range limitation feature. Collisions and resulting component damage can thus be avoided.

Overload warning device and load torque limitation

The audible and visual overload warning system continuously tells the operator about the current load situation of the machine. Furthermore, load torque limitation automatically regulates the speed of the working hydraulics to allow the maximum load bearing capacity to be approached safely. In the event of an overload, the functions which could cause the machine to topple are disabled. Only movements back to the safe working range are then possible.

High machine availability

Quality and competence

Our experience, understanding of customer needs and the technical implementation of these findings guarantee the success of our products. For decades, Liebherr has been inspirational with its depth of production and system solutions. Key components such as the diesel engine, electronic components, slew ring, swivel drive and hydraulic cylinders are developed and produced by Liebherr itself. The great extent of in-house manufacturing guarantees maximum quality and ensures that components are optimally configured to each other.

Robust design

All steel components are designed and manufactured by Liebherr. High-strength steel plates configured for the toughest of requirements result in high torsional stiffness and optimum absorption of forces to give a longer service life.

Intelligent self diagnostics

The innovative control electronics permanently monitor the vital functions of the machine to guarantee a high level of machine availability. Components which are critical for safety have a secondary redundancy feature to guarantee maximum safety and reliability.



QPDM – quality and process data management

- QPDM allows production data to be logged, documented and evaluated
- Test specifications and machine documented automatically logged
- Ability to handle large quantities of data while maintaining uniform high quality



Piston rod protection


- Maximum protection of piston rod
- Robust construction of hot-dip galvanized steel for a long service life in tough applications
- Available for outriggers, hoist cylinders, ERC cylinder and tip cylinder as an option



Equipment

- Components enhanced using FEM for maximum service life even if subjected to heavy lateral stresses during demanding tasks
- Cables routed internally to protect them from damage
- High load capacities with long reaches
- Reaches up to 62ft

Comfort



Perfection at a glance – when technology is comfortable

The Liebherr deluxe cab is spacious, has an ergonomic design and is very quiet. This ensures that the operator is able to fully focus throughout the working day.

Deluxe cab

Ergonomic design

The cab design provides excellent conditions for healthy, focused and productive work in maximum comfort. The color touchscreen display, the controls and operator's comfort seat are all coordinated to form a perfect ergonomic unit. In addition the ergonomic joysticks allow the machine operation to be both pleasant and precise.

Excellent all around vision

The large areas of glass, different versions of cab elevations and the rear and side area monitoring systems provide the operator with an excellent view of his working area and the zone around the machine. This perfect view enhances the operator's safety and ensures that he can handle the machine safely at all times.

Low noise levels

The use of viscoelastic mounts, good insulation and low noise diesel engines from Liebherr minimises noise emissions and vibrations. Both electric and diesel-powered machines produce extremely low sound levels, which means they are classed as low-noise machines that are not harmful to people and the environment.

Comfortable operation

Proportional control

Precision control of the material handling machine is especially important in applications such as waste separation or scrap recycling. Thanks to the standard proportional control, even such demanding operations can be mastered with ease.

Joystick steering and stabilizing

The standard joystick steering gives the operator an additional comfort boost. The steering movement can be conveniently executed using the joystick, eliminating the need to reposition during the work cycle. Substituting the steering wheel in favor of joystick steering provides additional legroom and a clear view of the working area. A standard feature is the control of the outriggers with the joystick for more comfort and an increased productivity of the machine.

Color touchscreen display and operation unit

The 9" color touchscreen display is intuitive in its operation and provides continuous information about all important operating data. The shortcut keys can be individually assigned and are selected quickly and easily with the menu strip.





Safe access

- Foldable left arm console, as well as wide, non-slip steps, catwalks and platforms, and ergonomically positioned handles for easy and safe
- All access systems are designed to national guidelines and statutory regulations
- Sliding door for comfortable entry with narrow platforms is available as an option



Comfort operator's seat with adjustable armrests


- Greater seating comfort due to variable damper hardness, lockable horizontal suspension, pneumatic lumbar support, seat heating and passive seat air conditioning for concentrated working
- Individual adjustment options for armrests, seat cushion depth, seat angle and head restraint for healthful working



Joystick with proportional control

- Good functionality with streamlined, ergonomic design
- 4-way mini joystick can be used to control all operations e.g. steering, outriggers and attachments etc.
- Joysticks each with two buttons and a rocker switch - increase the number of functions available

Maintainability



Efficiency bonus – even with maintenance and service

The Liebherr LH 40 and LH 50 material handling machines are powerful, robust, precise and efficient. They also feature integral maintenance benefits as a result of their service-based design. All maintenance work for Liebherr material handlers can be carried out quickly, easily and safely. This minimizes the machine's maintenance costs and downtime.

Efficient maintenance concept

Service-based machine design

The service-based machine design guarantees short servicing times, thus minimizing maintenance costs. All the service points are positioned in close proximity to one another, are easily accessible from the ground or on catwalks and platforms, and easy to reach thanks to the large, wide-opening service doors. This means that service work can be completed even more quickly and efficiently.

Integral maintenance benefits

Maintenance work helps to keep the machine fully functional. However this kind of work leads to machine downtimes which must be minimized. With change intervals of up to 2,000 hours for engine oil and up to 8,000 hours for hydraulic oil, Liebherr has significantly reduced the amount of maintenance and increased the productivity of the material handlers. In addition, central lubrication systems minimize daily maintenance. Above all, electric material handling machines are characterized by their low maintenance requirements.

Your competent service partner

Remanufacturing

The Liebherr remanufacturing program offers cost-effective reconditioning of components to the highest quality standards. Various reconditioning levels are available: Replacement components, general overhaul or repair. The customer receives components with original part quality at a reduced cost.

Competent advice and service

Competent advice is a given at Liebherr. Experienced specialist provide decision guidance for your specific requirements: application-oriented sales support, service agreements, economical repair alternatives, original parts management, as well as remote data transmission for machine planning and fleet management.



Lubrication as it works

- Fully automatic central lubrication system for uppercarriage and equipment
- Fully automatic central lubrication system for the undercarriage available as an option
- Lubricates without interrupting work to ensure better productivity and a long component service life



Servicing advantages for electrical machines

- Low operating and maintenance costs
- Significantly longer maintenance intervals compared to diesel engines due to a lower number of wear parts
- Cost savings on servicing
- Maximum productivity due to permanent readiness of the machine



Rapid spare parts service

- 24-hour delivery: Spare parts service is available for our dealers around the clock
- Electronic spare parts catalogue:
 Fast and reliable selection and ordering via the Liebherr online portal
- With online tracking, the current processing status of your order can be viewed at any time

Material handling machines overview

Equipment

- High load capacities and long reach thanks to optimized kinematic properties and robust construction for greater handling performance
- Energy recovery cylinder filled with nitrogen for maximum efficiency through less energy consumption at more handling capacity
- Pipe fracture safety valves on hoist and stick cylinders and retract stick shut-off for maximum safety during every application
- Quick coupling systems and attachments made by Liebherr for maximum machine capacity, utilization and greater handling performance

Operator's cab

- Joystick steering without steering column as standard for convenient operation, greater legroom and clear view of the working area
- Less strain on the operator, workers and reduced environmental pollution due to lower noise emissions
- Optimum visibility thanks to large glass surfaces and standard rear and side area monitoring with camera
- Proportional control is standard with 4-way mini joystick for greater precision, high precision control and functions





Uppercarriage


- 2-circuit Liebherr-Synchron-Comfort-system (LSC) with LUDV technology for faster working speed at up to 20% less energy consumption
- 155 kW engine output and greater pump flow for fast work cycles, convincing dynamics and maximum handling performance
- Electrical pilot control enables individual settings for the operator and an end position damping of the equipment
- Reduction in operating costs thanks to built-in maintenance advantages and optimum service accessibility
- Frequency converter provides the direct energy supply and control for the electric motor*

Undercarriage


- Optimized hydraulics with closed slewing mechanism circuit for greater energy efficiency and faster work cycles
- Central lubrication system (manual / full automatic) for more productive working time (optional available)
- Load-holding valves fitted as standard on all support cylinders for maximum stability in every application
- Less downtime thanks to maintenance-free support cylinders
- Different cable variants for flexible applications and high mobility*

^{*} only with electric

The perfect solution for every application



Cab elevations









Hydraulic cab elevation

30° tilt function

Rigid cab elevation







Turret elevations

Diesel



Undercarriage





Mobile

Crawler

Examples of use



LH 50 M Industry Litronic in scrap handling operation



Container dismantling with the LH 40 M Industry Litronic



LH 50 M Industry Litronic in trailer operation when handling logs



Scrap handling with the LH 50 M Industry Litronic



Loading extruded aluminium bundles onto wagons with the LH 50 M Industry Litronic



Loading a concrete mixing plant with the LH 40 M Industry Litronic



LH 50 C High Rise Industry Litronic loading waste wood



LH 40 M Industry Litronic for disassembling steel girders with a scrap shear

Technical data

Diesel engine

- Diesei eligilie	
Rating	
per SAE J1349	208 HP (155 kW) at 1,800 rpm
per ISO 9249	211 HP (155 kW) at 1,800 rpm
Model	Liebherr D934
Туре	4 cylinder in-line
Bore / Stroke	4.8/5.9 in
Displacement	427,17 in ³
Engine operation	4-stroke diesel
	Common-Rail
	Turbo-charged and after-cooled
	Reduced emissions
Air cleaner	Dry-type air cleaner with pre-cleaner, primary and safety
	elements
Engine idling	Sensor controlled
Electrical system	
Voltage	24 V
Batteries	2 x 180 Ah / 12 V
Alternator	Three-phase current 28V/140A
Stage V	
Harmful emissions values	According to regulation (EU) 2016/1628
Emission control	Liebherr-SCRFilter technology
Fuel tank	120 gal
Urea tank	17 gal
Stage IIIA (compliant)	
Harmful emissions values	In accordance with ECE-R.96 Power Band H
Fuel tank	120 gal
Tier 4 Final	
Harmful emissions values	In accordance with 40CFR1039 (EPA) / 13CCR (CARB)
Emission control	Liebherr-SCR technology
Fuel tank	120 gal
Urea tank	17 gal

Electric motor

Rating	145 kW at 1,800 rpm
Туре	Three-phase squirrel cage motor
Secondary electric motor	Electric motor auxiliary equipment (air-conditioning compressor, alternator 24V) 15kW
Electrical system energy supply	Frequency converter fed drive system Heavy-duty version
Supply voltage	
Low voltage	380 V, 400 V
Frequency	50/60Hz
Engine idling	Sensor controlled
Electrical system	Battery-assisted
	Control system, lighting, diagnostics system
Voltage	24V
Batteries	2 x 135 Ah/12 V
Alternator	Three-phase current 28 V / 140 A

 $Deviating\ parameters\ of\ the\ power\ supply\ system\ must\ always\ be\ clarified\ with\ Liebherr-Hydraulik bagger\ GmbH.$

\approx Cooling system

Cooming system	
Diesel engine	Water-cooled Compact cooling system consisting cooling unit for water, hydraulic oil and charge air with stepless thermo- statically controlled fan
Electric motor	Air-cooled Cooling system for hydraulic oil with an infinitely variable, thermostatically controlled fan drive system

Hydraulic controls

II/aiaaiio ooiitiois	
Power distribution	Via control valves with integrated safety valves, simulta- neous actuation of chassis and equipment. Swing drive in separate closed circuit
Servo circuit	
Equipment and swing	With electro-hydraulic pilot control and proportional joystick levers
Chassis mobile	Electro-proportional via foot pedal
Chassis crawler	With electric proportionally functioning foot pedals or adjusted with plugable levers
Additional functions	Via switch or electro-proportional foot pedals
Proportional control	Proportionally acting transmitters on the joysticks for additional hydraulic functions

Hydraulic system

, ,	
Hydraulic pump	
For equipment and travel drive	2 Liebherr axial piston variable displacement pumps (double construction)
Max. flow	2 x 63 gpm
Max. pressure	5,076 psi
For swing drive	Reversible axial piston variable displacement pump, closed-loop circuit
Max. flow	38 gpm
Max. pressure	5,366 psi
Hydraulic pump regulation and control	2 circuit Liebherr-Synchron-Comfort-system (LSC) with electronic engine speed sensing regulation, pressure and flow compensation, automatic oil flow optimizer
Hydraulic tank	75 gal
Hydraulic system	160 gal
Filtration	1 main return filter with integrated partial micro filtration (5 µm)
MODE selection	Adjustment of engine and hydraulic performance via a mode pre-selector to match application, e.g. for espe- cially economical and environmentally friendly operation or for maximum material handling and heavy-duty jobs
S (Sensitive)	Mode for precision work and lifting through very sensitive movements
E (Eco)	Mode for especially economical and environmentally friendly operation
P (Power)	Mode for high performance with low fuel consumption
P+ (Power-Plus)	Mode for highest performance and for very heavy duty applications, suitable for continuous operation
Engine speed and performance setting	Stepless alignment of engine output and hydraulic power via engine speed
Option	Tool Control: 20 pre-adjustable pump flows and pressures for add-on attachments



\bigcirc Swing drive

Drive	Liebherr axial piston motor in a closed system, Liebherr planetary reduction gear
Swing ring	Liebherr, sealed race ball bearing swing ring, internal teeth
Swing speed	0-4.7 rpm stepless (LH 40) 0-5.0 rpm stepless (LH 50) 0-4.0 rpm stepless (High Rise)
Swing torque	61,955 lbf ft
Holding brake	Wet multi-disc (spring applied, pressure released)
Option	Slewing gear brake Comfort



Can	
Cab	TOPS safety cab structure (tip-over protection) with individual windscreens or featuring a slide-in subpart under the ceiling, work headlights integrated in the ceiling, a door with a sliding window (can be opened on both sides), large stowing and depositing possibilities, shock-absorbing suspension, sound damping insulating, tinted laminated safety glass, separate shades for the sunroof window and windscreen
High Rise	Deviating from standard: safety cab structure with fixed built-in front and roof window made from impact-resistant laminated safety glass
Operator's seat Comfort	Air cushioned operator's seat with 3D-adjustable arm- rests, headrest, lap belt, seat heater, adjustable seat cushion inclination and length, lockable horizontal sus- pension, automatic weight adjustment, adjustable sus- pension stiffness, pneumatic lumbar vertebrae support and passive seat climatization with active coal
Operator's seat Premium (Option)	In addition to operator's seat comfort: active electronic weight adjustment (automatic readjustment), pneumatic low frequency suspension and active seat climatization with active coal and ventilator
Arm consoles	Joysticks with control consoles and swivel seat, folding left control console
Operation and displays	Large high-resolution operating unit, self-explanatory, color display with touchscreen, video-compatible, numerous setting, control and monitoring options, e.g. air conditioning control, fuel consumption respectively energy consumption, machine and attachment parameters
Air-conditioning	
Diesel engine	Automatic air-conditioning, recirculated air function, fast de-icing and demisting at the press of a button, air vents can be operated via a menu; recirculated air and fresh air filters can be easily replaced and are accessible from the outside; heating-cooling unit, designed for extreme outside temperatures, sensors for solar radiation, inside and outside temperatures
Electric motor	In addition to diesel engine: stationary air conditioning function with external climate condenser - controlled by a weekly timer



Equipment

Туре	High-strength steel plates at highly-stressed points for the toughest requirements. Complex and stable mountings of equipment and cylinders
Hydraulic cylinders	Liebherr cylinders with special sealing and guide system and, depending on cylinder type, shock absorption
Energy recovering cylinder	Liebherr gas cylinder with special sealing and control system
Bearings	Sealed, low maintenance


● ● Undercarriage		
Mobile		
Versions	Standard, High Rise	
Drive	Oversized two speed power shift transmission with additional creeper speed, Liebherr axial piston motor with functional brake valve on both sides	
Travel speed Joystick steering	0-1.9 mph stepless (creeper speed + transmission stage 1) (Diesel) 0-1.5 mph stepless (creeper speed + transmission stage 1) (Electric) 0-3.1 mph stepless (transmission stage 1) 0-7.5 mph stepless (creeper speed + transmission stage 2) 0-7.5 mph stepless	
Travel speed Wheel steering (Option)	(transmission stage 2) O- 1.9 mph stepless (creeper speed + transmission stage 1) (Diesel) O- 1.5 mph stepless (creeper speed + transmission stage 1) (Electric) O- 3.1 mph stepless (transmission stage 1) O- 7.5 mph stepless (creeper speed + transmission stage 2) O- 7.5 mph stepless (transmission stage 2, only for High Rise) O-12.4 mph stepless (transmission stage 2, not for High Rise)	
Driving operation	Automotive driving using accelerator pedal, cruise control function: storage of variable accelerator pedal positions	
Axles	132,277 lb / 154,324 lb drive axles (LH 40 M / LH 50 M); manual or automatic hydraulically controlled front axle oscillation lock	
Option	Four wheel steering (LH 40 M)	
Option	Steering reversal control (LH 40 M)	
Service brake	Two circuit travel brake system with accumulator; wet and backlash-free disc brake	
Holding brake Stabilization	Wet multi-disc (spring applied, pressure released)	
Option	4 point outriggers Dozer blade, at the front, for 4 point outriggers (not for High Rise)	
Crawler	(iiot ioi riigii riioo)	
Versions	EW, SW, High Rise	
Drive	Liebherr compact planetary reduction gear with Liebherr axial piston motor per side of undercarriage	
Travel speed EW (LH 40) SW (LH 40)	0-2.7 mph stepless 0-1.9 mph stepless (creeper speed) 0-2.4 mph stepless	
High Rise (LH 50)	0-1.5 mph stepless (creeper speed) 0-2.3 mph stepless	
Droko	0-1.4mph stepless (creeper speed) Functional brake valves on both sides	
Brake Holding brake		
Track pads	Wet multi-disc (spring applied, pressure released) Triple grouser, flat	
Tracks	Sealed and greased	
	outura and groupou	



Lubrication	Liebherr central lubrication system for uppercarriage and equipment, automatically
Mobile (Option)	Liebherr central lubrication system for undercarriage, automatically
Steps system	Safe and durable access system with anti-slip steps; main components hot-galvanized
Noise emission	
ISO 6396	70 dB(A) = L _{pA} (inside cab)
2000/14/EC	103 dB(A) = L _{WA} (surround noise)

LH 40 M - Dimensions


Industry



^{*} For electric machines, the length of the machine is increased accordingly by the trailing cable/cable reel system. Detailed dimensions are available on request.

LH 40 M - Choice of cab elevation


Cab elevation LFC (rigid elevation)



Increase type	LFC 120
Height	3'11"
В	13' 7"
С	15' 3"
D	2' 7"

A rigid cab elevation has a fixed eye level height. For a lower transport height, the shell of the cab can be removed and replaced by a transport device. The dimension C is in this machine design for all rigid cab elevations 12'3".

Cab elevation LHC (hydraulic elevation)




Increase type	LHC 255
B1	9' 8"
B2	18'
C1	11' 2"
C2	19' 6"
D1	4' 5"
D2	4'10"
E	11'

The hydraulically adjustable cab allows the driver, that he can choose his field of view freely and at any time within the stroke.

Tires 12.00-20


LH 50 M - Dimensions

Industry



LH 50 M - Choice of cab elevation


Cab elevation LFC (rigid elevation)



Increase type	LFC 120
Height	3'11"
В	14' 3"
С	15'11"
D	2' 7"

A rigid cab elevation has a fixed eye level height. For a lower transport height, the shell of the cab can be removed and replaced by a transport device. The dimension C is in this machine design for all rigid cab elevations 13'.

Cab elevation LHC (hydraulic elevation)




Increase type	LHC 255	LHC 340-35
B1	10' 4"	11' 6"
B2	18' 8"	22' 8"
C1	12'	13' 1"
C2	20' 4"	24' 4"
D1	4' 5"	8' 1"
D2	4'10"	8' 1"
E	11' 8"	12'11"

The hydraulically adjustable cab allows the driver, that he can choose his field of view freely and at any time within the stroke.

Tires 16.00-25

LH 40 C - Dimensions


Industry



^{*} For electric machines, the length of the machine is increased accordingly by the trailing cable/cable reel system. Detailed dimensions are available on request.

LH 40 C - Choice of cab elevation


Cab elevation LFC (rigid elevation)



Increase type	LFC 120
Height B	3'11"
В	13' 1"
С	14' 8"
D	2' 7"

A rigid cab elevation has a fixed eye level height. For a lower transport height, the shell of the cab can be removed and replaced by a transport device. The dimension C is in this machine design for all rigid cab elevations 11'9".

Cab elevation LHC (hydraulic elevation)




Increase type	LHC 255
B1	9' 1"
B2	17' 6"
C1	10' 8"
C2	19'
D1	4' 5"
D2	4'10"
E	10' 5"

The hydraulically adjustable cab allows the driver, that he can choose his field of view freely and at any time within the stroke.


LH 50 M HR - Dimensions

Industry



LH 50 M HR - Cab elevation

Cab elevation LHC (hydraulic elevation)




Increase type	LHC 340-35
B1	15'4"
B2	26'6"
C1	17'1"
C2	28'3"
D1	8'
D2	8'2"

The hydraulically adjustable cab allows the driver, that he can choose his field of view freely and at any time within the stroke.

Tires 16.00-25


LH 50 C HR - Dimensions

Industry



LH 50 C HR - Cab elevation

Cab elevation LHC (hydraulic elevation)




Increase type	LHC 340-35
B1	17'3"
B2	28'5"
C1	19'
C2	30'3"
D1	8'2"
D2	8'2"

The hydraulically adjustable cab allows the driver, that he can choose his field of view freely and at any time within the stroke.


Kinematic variants




Kinematic variant 2A



Kinematic variant 2D / 2C







Altered range curve with additional reach depth, e.g. for unloading from ships

LH 40 M - Equipment GA13

Industry - Kinematic 2A



Dimensions



Operating weight

The operating weight includes the basic machine with 4 point outriggers, hydr. cab elevation, 8 solid tires plus intermediate rings, straight boom 24'11'', angled stick 19'8'' and multi-tine grab GMM $50-5/1.18\,yd^3$ semi-closed tines.

Weight	84.200 lb


1/			15ft		Oft 25ft		30	30 ft		ft	40	ft	45	ft	50	ft	55 ft		- AB		<u></u>	
↓⁄⁄ ft	Undercarriage		Ŀ	-5	Ŀ	-5	Ŀ	-5	Ŀ		ď	-5	Ŀ		Ŀ	-5	Ŀ		Ŀ			ftin
50	Stabilizers raised 4 pt. outriggers down		Diag	-3.0	Desc		bac	-555	0000		bac	-0.0	umu		und		oms.		unu	-000	CHIC	
45	Stabilizers raised 4 pt. outriggers down			18,3* 18,3*	18,3* 18,3*															15,3* 15,3*	15,3* 15,3*	22' 2"
40	Stabilizers raised 4 pt. outriggers down			20,5 21,5*	21,5* 21,5*	14,1 18,3*	17,9 18,3*													10,6 12,9*	12,9* 12,9*	29' 1"
35	Stabilizers raised 4 pt. outriggers down					14,5 18,3*	18,3* 18,3*	10,5 16,5*	13,4 16,5*											8,1 11,7*	10,6 11,7*	33'11"
30	Stabilizers raised 4 pt. outriggers down					14,5 18,2*	18,2* 18,2*	10,5 16,3*	13,5 16,3*	7,9 14,9*	10,2 14,9*									6,8 11,1*	8,9 11,1*	37' 5"
25	Stabilizers raised 4 pt. outriggers down			20,3 21,4*	21,4* 21,4*	14,2 18,6*	18,0 18,6*	10,4 16,5*	13,3 16,5*	7,8 14,9*	10,2 14,9*	5,9 10,8*	7,9 10,8*							5,9 10,7*	7,9 10,7*	40'
20	Stabilizers raised 4 pt. outriggers down			19,4 22,6*	22,6* 22,6*	13,6 19,3*	17,4 19,3*	10,0 16,9*	12,9 16,9*	7,6 15,0*	10,0 15,0*	5,9 12,4	7,9 13,4*							5,3 10,6*	7,2 10,6*	41'11"
15	Stabilizers raised 4 pt. outriggers down	28,1 31,0*	31,0* 31,0*	18,0 24,4*	23,4 24,4*	12,7 20,2*	16,5 20,2*	9,5 17,4*	12,4 17,4*	7,3 15,2*	9,7 15,2*	5,8 12,3	7,7 13,4*							5,0 10,6*	6,7 10,6*	43'
10	Stabilizers raised 4 pt. outriggers down	24,7 34,9*	33,5 34,9*	16,3 26,3*	21,6 26,3*	11,8 21,2*	15,5 21,2*	9,0 17,9*	11,8 17,9*	7,0 14,8	9,3 15,4*	5,6 12,1	7,5 13,2*							4,8 10,6	6,5 10,8*	43' 7"
5	Stabilizers raised 4 pt. outriggers down	21,5 37,5*	30,1 37,5*	14,7 27,6*	19,9 27,6*	10,9 21,9*	14,6 21,9*	8,4 18,1	11,2 18,1*	6,7 14,5	9,0 15,3*	5,4 11,9	7,3 12,9*							4,7 10,5	6,4 10,6*	43' 7"
0	Stabilizers raised 4 pt. outriggers down	19,6 22,0*	22,0* 22,0*	13,5 27,7*	18,6 27,7*	10,1 21,9*	13,8 21,9*	7,9 17,6	10,7 17,9*	6,4 14,1	8,7 14,8*	5,2 11,7	7,2 12,0*							4,7 9,6*	6,5 9,6*	43'
- 5	Stabilizers raised 4 pt. outriggers down	18,8 20,6*	20,6* 20,6*	12,9 26,1*	17,9 26,1*	9,6 20,8*	13,3 20,8*	7,6 16,8*	10,4 16,8*	6,2 13,6*	8,5 13,6*	5,2 10,1*	7,1 10,1*							5,1 9,7*	7,0 9,7*	40' 6"
-10	Stabilizers raised 4 pt. outriggers down			12,6 22,3*	17,6 22,3*	9,4 18,1*	13,0 18,1*	7,5 14,5*	10,3 14,5*											6,3 11,7*	8,7 11,7*	34' 2"

Height 🗝 Can be slewed through 360° 🖟 In longitudinal position of undercarriage 🥏 Max. reach * Limited by hydr. capacity


The lift capacities on the stick end without attachment are stated in lb x 1,000 and are valid on a firm, level supporting surface with blocked oscillating axle. These capacities can be slewed through 360° with the undercarriage in the transverse position. Capacities in the longitudinal position of the undercarriage (±15°) are specified over the steering axle with the stabilizers raised and over the rigid axle with the stabilizers down. Indicated loads based on the ISO 10567 standard and do not exceed 75% of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. This operating temperature is ensured by continuous movement of the boom. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capability of the hydraulic elements, or the maximum permissible lifting capacity of the load hook.

LH 40 M - Equipment GA14

Industry - Kinematic 2A



Dimensions



Operating weight

The operating weight includes the basic machine with 4 point outriggers, hydr. cab elevation, 8 solid tires plus intermediate rings, straight boom 28'3", angled stick 19'8" and multi-tine grab GMM 50-5/1.18 yd³ semi-closed tines.

Weight 84,900 lb


1/		15ft 20ft		ft	25	ft	30)ft	35	ft	40	ft	45ft		50	ft	55	ft			Ď.	
12/			P		P		P		P		P		P		P		P		P		F	ĺ
ft	Undercarriage			-5				-5	造	-		⊶ 5⊃	造	-5			쁘		반		쁘	ft in
50	Stabilizers raised 4 pt. outriggers down	21,6* 21,6*	21,6* 21,6*																	17,0* 17,0*	17,0* 17,0*	19' 6"
45	Stabilizers raised 4 pt. outriggers down			20,2 21,1*	21,1* 21,1*	13,8 17,5*	17,5* 17,5*													11,1 13,6*	13,6* 13,6*	28'
40	Stabilizers raised 4 pt. outriggers down					14,4 18,0*	18,0* 18,0*	10,3 16,0*	13,3 16,0*											8,0 12,2*	10,5 12,2*	33' 8"
35	Stabilizers raised 4 pt. outriggers down					14,5 17,8*	17,8* 17,8*	10,5 15,7*	13,5 15,7*	7,8 14,2*	10,1 14,2*									6,4 11,4*	8,5 11,4*	38'
30	Stabilizers raised 4 pt. outriggers down			20,6 21,0*	21,0* 21,0*	14,3 17,9*	17,9* 17,9*	10,4 15,7*	13,3 15,7*	7,8 14,1*	10,1 14,1*	5,8 12,4	7,8 12,7*							5,4 10,9*	7,3 10,9*	41' 1"
25	Stabilizers raised 4 pt. outriggers down			19,8 21,8*	21,8* 21,8*	13,7 18,4*	17,6 18,4*	10,1 16,0*	13,0 16,0*	7,6 14,2*	10,0 14,2*	5,8 12,4	7,8 12,7*							4,8 10,6	6,5 10,7*	43' 6"
20	Stabilizers raised 4 pt. outriggers down	28,0* 28,0*	28,0* 28,0*	18,4 23,1*	23,1* 23,1*	12,9 19,1*	16,8 19,1*	9,6 16,4*	12,5 16,4*	7,3 14,4*	9,6 14,4*	5,7 12,2	7,6 12,7*	4,4 9,9	6,0 11,1*					4,3 9,9	6,0 10,6*	45' 2"
15	Stabilizers raised 4 pt. outriggers down	25,6 32,5*	32,5* 32,5*	16,7 24,6*	22,0 24,6*	11,9 20,0*	15,7 20,0*	8,9 16,9*	11,8 16,9*	6,9 14,6*	9,2 14,6*	5,4 12,0	7,4 12,8*	4,3 9,9	6,0 11,0*					4,0 9,4	5,6 10,5*	46' 4"
10	Stabilizers raised 4 pt. outriggers down	21,6 35,4*	30,2 35,4*	14,7 26,1*	19,9 26,1*	10,8 20,7*	14,5 20,7*	8,2 17,3*	11,1 17,3*	6,5 14,3	8,8 14,7*	5,2 11,7	7,1 12,7*	4,1 9,7	5,8 10,8*					3,8 9,1	5,4 9,8*	46'10"
5	Stabilizers raised 4 pt. outriggers down	13,0* 13,0*	13,0* 13,0*	13,0 26,7*	18,1 26,7*	9,8 21,1*	13,4 21,1*	7,6 17,3	10,4 17,4*	6,1 13,8	8,4 14,6*	4,9 11,4	6,8 12,4*	4,0 9,6	5,7 10,2*					3,8 9,0	5,3 9,1*	46'10"
0	Stabilizers raised 4 pt. outriggers down	11,5* 11,5*	11,5* 11,5*	11,9 26,0*	17,0 26,0*	9,0 20,7*	12,6 20,7*	7,1 16,7	9,9 17,0*	5,7 13,5	8,0 14,2*	4,7 11,2	6,6 11,8*	3,9 9,2*	5,6 9,2*					3,8 8,2*	5,4 8,2*	46' 4"
- 5	Stabilizers raised 4 pt. outriggers down	13,1* 13,1*	13,1* 13,1*	11,4 23,6*	16,4 23,6*	8,6 19,3*	12,1 19,3*	6,8 15,9*	9,6 15,9*	5,5 13,1*	7,8 13,1*	4,6 10,5*	6,5 10,5*							4,1 8,3*	5,8 8,3*	43' 8"
-10	Stabilizers raised 4 pt. outriggers down			11,2 19,6*	16,2 19,6*	8,4 16,6*	11,9 16,6*	6,6 13,8*	9,4 13,8*	5,4 11,1*	7,7 11,1*									5,0 9,8*	7,0 9,8*	37' 6"

Height Gan be slewed through 360° In longitudinal position of undercarriage Max. reach *Limited by hydr. capacity


The lift capacities on the stick end without attachment are stated in lb x 1,000 and are valid on a firm, level supporting surface with blocked oscillating axle. These capacities can be slewed through 360° with the undercarriage in the transverse position. Capacities in the longitudinal position of the undercarriage (±15°) are specified over the steering axle with the stabilizers raised and over the rigid axle with the stabilizers down. Indicated loads based on the ISO 10567 standard and do not exceed 75% of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. This operating temperature is ensured by continuous movement of the boom. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capability of the hydraulic elements, or the maximum permissible lifting capacity of the load hook.

LH 40 M - Equipment GA16

Industry - Kinematic 2A



Dimensions



Operating weight

The operating weight includes the basic machine with 4 point outriggers, hydr. cab elevation, 8 solid tires plus intermediate rings, straight boom $29^{\circ}10^{\circ}$, angled stick $22^{\circ}4^{\circ}$ and multi-tine grab GM $65/0.78\,\mathrm{yd}^3$ semi-closed tines.

Weight 84,900 lb


1		15	15ft		20 ft		25 ft		30 ft		ift	40)ft	45	ft	50	ft	55 ft				₹
10			P		P		P		P		P		P		P		P		P		P.	ĺ
ft	Undercarriage	− €		50		-5		-40		₽		-5	밤		빤	€	빤	 €	반			ft in
55	Stabilizers raised			19,5*	19,5*															16,3*	16,3*	18' 4"
	4 pt. outriggers down Stabilizers raised			19,5*	19,5*	18.9*	18,9*	14,1	15,9*											16,3* 11.1	16,3* 12,6*	
50	4 pt. outriggers down					18,9*	18,9*	15,9*	15,9*											12,6*	12,6*	28' 2"
45	Stabilizers raised 4 pt. outriggers down							14,8 17,3*	17,3* 17,3*	10,6 15,2*	13,6 15,2*									7,7 11,0*	10,1 11,0*	34' 7"
	Stabilizers raised							15,2	16,9*	10,9	13,2	8.0	10.4							6,0	8,0	
40	4 pt. outriggers down							16,9*	16,9*	14,9*	14,9*	13,4*	13,4*							10,1*	10,1*	39' 5"
35	Stabilizers raised							15,1	16,9*	11,0	14,0	8,1	10,5	6,0	8,0					4,9	6,7	43'
	4 pt. outriggers down Stabilizers raised							16,9* 14,8	16,9* 17,1*	14,8* 10,7	14,8* 13,7	13,2* 8,0	13,2* 10,4	12,0*	12,0* 8,0	4,5	6,2			9,6* 4,2	9,6* 5,9	
30	4 pt. outriggers down							17,1*	17,1*	14,9*	14,9*	13,3*	13,3*	12,0*	12,0*	10,1	10,8*			9,3*	9,3*	45'11"
25	Stabilizers raised					20,5	20,9*	14,1	17,6*	10,3	13,3	7,7	10,1	5,9	7,9	4,5	6,2			3,7	5,3	48'
23	4 pt. outriggers down Stabilizers raised					20,9* 19.0	20,9*	17,6*	17,6*	15,2*	15,2*	13,4*	13,4*	12,0*	12,0*	10,1	10,8*			8,9	9,1*	10
20	4 pt. outriggers down					22,1*	22,1* 22,1*	13,2 18,3*	17,1 18,3*	9,7 15,6*	12,6 15,6*	7,3 13,7*	9,7 13,7*	5,6 12,1*	7,6 12,1*	4,3 10,0	10,8*			3,4 8,3	4,9 9,1*	49' 6"
15	Stabilizers raised			26,3	31,2*	16,9	22,4	12,0	15,8	8,9	11,8	6,8	9,2	5,3	7,3	4,1	5,8	3,2	4,7	3,1	4,6	50' 6"
13	4 pt. outriggers down			31,2*	31,2*	23,6*	23,6*	19,1*	19,1*	16,1*	16,1*	13,9*	13,9*	11,9	12,2*	9,8	10,7*	8,1	9,2*	7,9	8,9*	30 6
10	Stabilizers raised 4 pt. outriggers down			21,7 34,0*	30,3 34.0*	14,7 25.0*	19,9 25,0*	10,7 19.9*	14,4 19,9*	8,1 16.5*	11,0 16,5*	6,3 14.1*	8,6 14.1*	5,0 11,5	6,9 12,2*	3,9 9,5	5,6 10,6*	3,1 8.0	4,6 8.9*	3,0 7.7	4,4 8.4*	51'
-	Stabilizers raised			11,9*	11,9*	12,6	17,7	9,4	13,1	7,3	10,1	5,8	8,1	4,6	6,5	3,7	5,4	3,0	4,5	2,9	4,3	F31
5	4 pt. outriggers down			11,9*	11,9*	25,8*	25,8*	20,3*	20,3*	16,7*	16,7*	13,6	14,1*	11,1	12,1*	9,3	10,3*	7,9	8,4*	7,6	7,8*	51'
0	Stabilizers raised			9,7* 9,7*	9,7* 9,7*	11,2 25,3*	16,2 25,3*	8,5	12,1 20,1*	6,7	9,5 16,5*	5,3	7,6 13,8*	4,3	6,2	3,5	5,2 9,8*	2,9 7.4*	4,4 7.4*	2,9 7.0*	4,3 7,0*	50' 6"
	4 pt. outriggers down Stabilizers raised			10,8*	10,8*	10,4	15,4	20,1* 7,9	11,4	16,3 6,2	9,0	13,1 5,0	7,3	10,8 4,1	11,7* 6,0	9,1 3,4	5,1	7,4	7,4"	3,0	4,6	
- 5	4 pt. outriggers down			10,8*	10,8*	22,4*	22,4*	19,0*	19,0*	15,7*	15,7*	12,7	13,1*	10,6	10,9*	8,8*	8,8*			6,8*	6,8*	48' 8"
-10	Stabilizers raised					10,1	15,0	7,5	11,1	5,9	8,7	4,8	7,1	4,0	5,9					3,5	5,2	44'
	4 pt. outriggers down Stabilizers raised					20,2*	20,2*	16,9*	16,9*	14,1*	14,1*	11,7*	11,7*	9,5*	9,5*					7,6*	7,6*	
-15	4 pt. outriggers down																					

Height 🕒 Can be slewed through 360° 🖟 In longitudinal position of undercarriage 🥌 Max. reach * Limited by hydr. capacity

The lift capacities on the stick end without attachment are stated in lb x 1,000 and are valid on a firm, level supporting surface with blocked oscillating axle. These capacities can be slewed through 360° with the undercarriage in the transverse position. Capacities in the longitudinal position of the undercarriage (±15°) are specified over the steering axle with the stabilizers raised and over the rigid axle with the stabilizers down. Indicated loads based on the ISO 10567 standard and do not exceed 75% of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. This operating temperature is ensured by continuous movement of the boom. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capability of the hydraulic elements, or the maximum permissible lifting capacity of the load hook.

LH 40 M - Equipment AF15

Industry - Kinematic 2D



1/			ft	20 ft		25ft		30 ft		35	ft	40	ft	45	ft	50	ft	55 ft				7
16/			P		P		P		P		P		P		P		P		P		P i	ĺ
ft	Undercarriage	-5		-€	쁘	-5		~5	쁘	-5	쁘	~5	쁩	₽	쁘		쁘		쁘	- -€	법	ft in
50	Stabilizers raised 4 pt. outriggers down					12,3* 12,3*	12,3* 12,3*													10,7* 10,7*	10,7* 10,7*	26'11"
45	Stabilizers raised 4 pt. outriggers down					,-	,-	11,4 12,5*	12,5* 12,5*											9,0 9,4*	9,4* 9,4*	33' 7"
40	Stabilizers raised 4 pt. outriggers down							11,8 12,6*	12,6* 12,6*	8,7 11,6*	11,1 11,6*									6,9 8,8*	8,8* 8,8*	38' 6"
35	Stabilizers raised 4 pt. outriggers down							11,9 12,5*	12,5* 12,5*	8,8 11,5*	11,2 11,5*	6,5 10,7*	8,5 10,7*							5,7 8,4*	7,5 8,4*	42' 2"
30	Stabilizers raised 4 pt. outriggers down							11,7 12,6*	12,6* 12,6*	8,7 11,5*	11,2 11,5*	6,6 10,6*	8,6 10,6*	4,8 8.3*	6,6 8,3*					4,8 8,2*	6,5 8,2*	45' 1"
25	Stabilizers raised 4 pt. outriggers down							11,3 12,9*	12,9* 12,9*	8,5 11,7*	10,9 11,7*	6,4 10,7*	8,4 10,7*	4,8 9,9*	6,6 9,9*					4,2 8,1*	5,8 8,1*	47' 4"
20	Stabilizers raised 4 pt. outriggers down					14,7 15,2*	15,2* 15,2*	10,7 13,4*	13,4* 13,4*	8,1 12,0*	10,5 12,0*	6,2 10,9*	8,2 10,9*	4,7 10,0*	6,4 10,0*					3,8 8,1*	5,3 8,1*	48'10"
15	Stabilizers raised 4 pt. outriggers down			19,5 19,5*	19,5* 19,5*	13,5 16,3*	16,3* 16,3*	10,0 14,1*	12,9 14,1*	7,5 12,4*	9,9 12,4*	5,8 11,1*	7,8 11,1*	4,5 10,1*	6,2 10,1*					3,4 8,3*	4,9 8,3*	49'11"
10	Stabilizers raised 4 pt. outriggers down	26,3 28,4*	28,4* 28,4*	17,1 21,5*	21,5* 21,5*	12,1 17,4*	16,0 17,4*	9,1 14,8*	12,0 14,8*	6,9 12,8*	9,3 12,8*	5,4 11,4*	7,4 11,4*	4,2 9,9	5,9 10,2*	3,3 8,2	4,8 9,1*			3,2 8,1	4,7 8,5*	50' 5"
5	Stabilizers raised 4 pt. outriggers down	21,6 31,7*	30,3 31,7*	14,7 23,3*	20,0 23,3*	10,7 18,5*	14,5 18,5*	8,1 15,4*	11,0 15,4*	6,3 13,2*	8,7 13,2*	5,0 11,6*	7,0 11,6*	4,0 9,6	5,7 10,2*	3,1 8,1	4,6 8,9*			3,1 8,0	4,6 8,8*	50' 4"
0	Stabilizers raised 4 pt. outriggers down	18,1 20,7*	20,7* 20,7*	12,7 24,4*	17,8 24,4*	9,5 19,2*	13,2 19,2*	7,3 15,8*	10,2 15,8*	5,8 13,5*	8,1 13,5*	4,6 11,2	6,6 11,7*	3,7 9,3	5,4 10,1*	,				3,0 8,0	4,5 8,6*	49'10"
- 5	Stabilizers raised 4 pt. outriggers down	16,3 16,9*	16,9* 16,9*	11,3 24,7*	16,4 24,7*	8,5 19,4*	12,2 19,4*	6,7 16,0*	9,5 16,0*	5,3 13,1	7,6 13,4*	4,3 10,8	6,3 11,5*	3,5 9,1	5,2 9,8*					3,1 8,1	4,6 8,3*	48'10"
-10	Stabilizers raised 4 pt. outriggers down	15,4 16,8*	16,8* 16,8*	10,5 23,8*	15,5 23,8*	7,9 19,0*	11,5 19,0*	6,2 15,6*	9,0 15,6*	5,0 12,8	7,3 13,0*	4,1 10,6	6,0 11,0*	3,4 9.0*	5,1 9.0*					3,2 7,9*	4,8 7,9*	47' 2"
-15	Stabilizers raised 4 pt. outriggers down	15,2 17.8*	17,8* 17.8*	10,2 21.7*	15,2 21.7*	7,6 17.6*	11,2 17,6*	5,9 14,5*	8,7 14,5*	4,8 12,0*	7,1 12,0*	4,0 9.8*	5,9 9.8*	.,0	.,0					3,5 7.7*	5,2 7,7*	44' 5"
-20	Stabilizers raised 4 pt. outriggers down	,-	,-	,.	,-	7,5 15,1*	11,1 15,1*	5,9 12,4*	8,7 12,4*	4,8 10,1*	7,1 10,1*	,-	,-							4,8 10,0*	7,1 10,0*	35' 1"

Height Gan be slewed through 360° In longitudinal position of undercarriage


Max. reach

* Limited by hydr. capacity


The lift capacities on the stick end without attachment are stated in lb x 1,000 and are valid on a firm, level supporting surface with blocked oscillating axle. These capacities can be slewed through 360° with the undercarriage in the transverse position. Capacities in the longitudinal position of the undercarriage (±15°) are specified over the steering axle with the stabilizers raised and over the rigid axle with the stabilizers down. Indicated loads based on the ISO 10567 standard and do not exceed 75% of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. This operating temperature is ensured by continuous movement of the boom. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capability of the hydraulic elements, or the maximum permissible lifting capacity of the load hook.

LH 40 M - Equipment GS11

Industry - Kinematic 2A



Dimensions



Operating weight

The operating weight includes the basic machine with 4 point outriggers, hydr. cab elevation, 8 solid tires plus intermediate rings, straight boom 24'11", stick HD with tipping kinematics special 11'10", quick coupler SWA 66 and scrap shear Genesis GXT 445R.

Weight 95,000 lb

The stick cylinder must be limited to the measure of 8'11".


	<u>1</u>		ft in
-000 000	-500 000	-000 000	1
		7,4 8,1* 8,1* 8,1*	26' 5"
		5,7* 5,7*	31' 7"
		4,3* 4,3*	35' 5"
		3,4* 3,4*	38' 1"
		- 0,2 2,8* 2,8*	40'
		2,3* 2,3*	41' 4"
		1,9* 1,9*	41'11"
		1,6* 1,6*	41'10"
		1,2* 1,2*	41' 2"
		0,6* 0,6*	40'
			38'
			34' 4"
			3,1 5,7* 5,7* 5,7* 5,7* 5,7* 0,7 3,2 4,3* 4,3* - 1,4 3,4* 3,4* - 0,2 2,8* 2,8* - 2,3* 2,3* - 1,9* 1,9* 1,6* 1,6* 1,2* 1,2* - 0,6* 0,6*

Height — Can be slewed through 360° In longitudinal position of undercarriage — Max. reach * Limited by hydr. capacity


The lift capacities on the stick end without attachment are stated in lb x 1,000 and are valid on a firm, level supporting surface with blocked oscillating axle. These capacities can be slewed through 360° with the undercarriage in the transverse position. Capacities in the longitudinal position of the undercarriage (±15°) are specified over the steering axle with the stabilizers raised and over the rigid axle with the stabilizers down. Indicated loads based on the ISO 10567 standard and do not exceed 75% of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. The values are calculated for the static state of the energy recovery cylinder. The maximum lift capacity for the quick coupler's load hook is 26,500 lb. Without attachment the lift capacity will increase by 11,023 lb and without quick coupler, tipping cylinder, lever and connection link by an additional 3,115 lb. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capability of the hydraulic elements, or the maximum permissible lifting capacity of the load hook.

LH 40 M - Equipment GSV14

Industry - Kinematic 2A



Dimensions



Operating weight

The operating weight includes the basic machine with 4 point outriggers, hydr. cab elevation, 8 solid tires plus intermediate rings, straight boom $24^{\circ}11^{\circ}$, stick HD with tipping kinematics special $11^{\circ}10^{\circ}$, quick coupler SWA 66, stick extension $8^{\circ}10^{\circ}$ and multi-tine grab GM $65/0.78\,\mathrm{yd^3}$ semi-closed tines.

Weight 88,600 lb

1		15	15 ft 20 ft		20 ft 25 ft			30	ft	35 ft		40 ft		45ft		50 ft		55 ft		AB 38		٦
ft	Undercarriage		Ŀ		Ŀ		Ŀ		Ŀ		Ď		Ŀ		Ů		Ŀ		Ŀ		B	ft in
50	Stabilizers raised 4 pt. outriggers down	17,3* 17,3*	17,3* 17,3*																	17,1* 17,1*	17,1* 17,1*	15' 1"
	Stabilizers raised 4 pt. outriggers down			17,4* 17,4*	17,4* 17,4*	11,9 12,3*	12,3* 12,3*													11,6 12,0*	12,0* 12,0*	25' 2"
	Stabilizers raised 4 pt. outriggers down					13,0 16,1*	16,1* 16,1*	8,4 12,3*	11,4 12,3*											7,3 10,1*	10,1* 10,1*	31' 6"
	Stabilizers raised 4 pt. outriggers down					13,4 15,6*	15,6* 15,6*	8,9 13,6*	11,9 13,6*	5,7 10,8*	8,1 10,8*									5,2 9,0*	7,5 9,0*	35'11"
	Stabilizers raised 4 pt. outriggers down					13,3 15,4*	15,4* 15,4*	8,9 13,4*	11,9 13,4*	5,9 11,8*	8,3 11,8*									3,9 8,4*	6,0 8,4*	39' 4"
	Stabilizers raised 4 pt. outriggers down					12,8 15,6*	15,6* 15,6*	8,6 13,4*	11,6 13,4*	5,8 11,7*	8,2 11,7*	3,7 10,3*	5,7 10,3*							3,1 8,1*	5,0 8,1*	41'10"
	Stabilizers raised 4 pt. outriggers down			18,3 19,4*	19,4* 19,4*	11,9 16,0*	15,8 16,0*	8,0 13,6*	11,0 13,6*	5,4 11,8*	7,8 11,8*	3,6 10,3*	5,6 10,3*							2,5 7,9*	4,3 7,9*	43' 6"
	Stabilizers raised 4 pt. outriggers down	23,2* 23,2*	23,2* 23,2*	16,3 20,6*	20,6* 20,6*	10,6 16,7*	14,5 16,7*	7,2 13,9*	10,2 13,9*	4,9 11,9*	7,3 11,9*	3,3 10,0	5,3 10,2*							2,1 7,9	3,9 7,9*	44' 8"
	Stabilizers raised 4 pt. outriggers down	22,4 29,6*	29,6* 29,6*	13,8 21,9*	19,2 21,9*	9,2 17,3*	13,0 17,3*	6,3 14,2*	9,3 14,2*	4,4 12,0*	6,7 12,0*	3,0 9,6	5,0 10,1*	1,9 7,6	3,6 7,9*					1,9 7,5	3,6 7,8*	45' 2"
	Stabilizers raised 4 pt. outriggers down	17,6 31,6*	26,2 31,6*	11,4 22,9*	16,6 22,9*	7,8 17,8*	11,5 17,8*	5,5 14,4*	8,3 14,4*	3,8 11,7	6,2 11,9*	2,6 9,2	4,6 9,7*	1,8 7,2*	3,5 7,2*					1,8 7,0*	3,4 7,0*	45' 2"
0	Stabilizers raised 4 pt. outriggers down	14,4 25,0*	22,6 25,0*	9,5 22,9*	14,6 22,9*	6,6 17,7*	10,3 17,7*	4,7 14,1*	7,6 14,1*	3,4 11,2	5,7 11,4*	2,4 8,9	4,3 9,0*							1,7 6,0*	3,4 6,0*	44' 7"
- 5	Stabilizers raised 4 pt. outriggers down	12,8 20,4*	20,4* 20,4*	8,3 21,6*	13,3 21,6*	5,8 16,7*	9,4 16,7*	4,2 13,2*	7,0 13,2*	3,0 10,4*	5,3 10,4*	2,2 7,6*	4,1 7,6*							1,9 5,8*	3,7 5,8*	42' 6"
-10	Stabilizers raised 4 pt. outriggers down	12,3 21,1*	20,2 21,1*	7,8 18,4*	12,7 18,4*	5,4 14,5*	8,9 14,5*	3,9 11,3*	6,7 11,3*	2,9 8,4*	5,1 8,4*		,.							2,5 6,9*	4,6 6,9*	37' 5"

The lift capacities on the end of the stick extension without attachment are stated in lb x 1,000 and are valid on a firm, level supporting surface with blocked oscillating axle. These capacities can be slewed through 360° with the undercarriage in the transverse position. Capacities in the longitudinal position of the undercarriage (±15°) are specified over the steering axle with the stabilizers raised and over the rigid axle with the stabilizers down. Indicated loads based on the ISO 10567 standard and do not exceed 75% of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. This operating temperature is ensured by continuous movement of the boom. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capacities of the hydraulic elements, or the maximum permissible lifting capacity of the load hook.


Max. reach * Limited by hydr. capacity

In longitudinal position of undercarriage


Height Can be slewed through 360°

LH 50 M - Equipment GA16

Industry - Kinematic 2A



Dimensions



Operating weight

The operating weight includes the basic machine with 4 point outriggers, hydr. cab elevation, 4 solid tires, straight boom 29'10", angled stick 22'4" and multi-tine grab GMM 50-5/1.44 yd 3 semiclosed tines.

Weight	97.000 lb

16		15 ft 20 ft		25	ft	30)ft	35	ift	40	ft	45	ft	50	ft	55	ft	-	~ <u>G</u>	_		
16/			P		P		P		₽		₽		₽		P		P		P		Ψ,	ĺ
ft	Undercarriage	⊶ 5	밥	⊶5)	밥	⊶ 5	밥	⊶5)	峼	− ₹	밤	⊶ 5⊃	밤	− ₽	밤	-5	밤	− 5	밥	⊶5	밤	ft in
60	Stabilizers raised 4 pt. outriggers down																					
55	Stabilizers raised 4 pt. outriggers down			15,9* 15.9*	15,9* 15,9*															15,3* 15,3*	15,3* 15,3*	20' 6"
50	Stabilizers raised 4 pt. outriggers down			20,7	20,7	16,5* 16,5*	16,5* 16,5*													12,2* 12,2*	12,2* 12,2*	29' 6"
45	Stabilizers raised 4 pt. outriggers down					18,3 18,4*	18,4* 18,4*	13,4 16,2*	16,2* 16,2*	9,9 11,7*	11,7* 11,7*									9,6 10,8*	10,8* 10,8*	35' 6"
40	Stabilizers raised 4 pt. outriggers down					18,0* 18,0*	18,0* 18,0*	13,7	16,0* 16,0*	10,3 14,5*	13,2 14,5*	7,7 10,2*	10,1 10,2*							7,7	10,0* 10,0*	40' 1"
35	Stabilizers raised 4 pt. outriggers down					18,0* 18,0*	18,0* 18.0*	13,6 15.9*	15,9* 15,9*	10,4 14.4*	13,2 14,4*	8,0 13.1*	10,3 13,1*							6,5 9,6*	8,6 9,6*	43' 7"
30	Stabilizers raised 4 pt. outriggers down					18,1 18,4*	18,4* 18,4*	13,4 16,1*	16,1* 16,1*	10,2 14,5*	13,1 14,5*	7,9 13,1*	10,3 13,1*	6,2 11,6*	8,2 11,6*					5,7 9,3*	7,7 9,3*	46' 4"
25	Stabilizers raised 4 pt. outriggers down			22,5* 22,5*	22,5* 22,5*	17,4 19.0*	19,0* 19.0*	12,9 16,5*	16,5 16,5*	9,9 14.7*	12,7 14.7*	7,8 13,2*	10,1 13,2*	6,1 12,0*	8,1 12,0*					5,2 9,1*	7,0 9,1*	48' 4"
20	Stabilizers raised 4 pt. outriggers down	22,9* 22,9*	22,9* 22,9*	23,2	24,0* 24,0*	16,4 19.9*	19,9* 19,9*	12,2 17,1*	15,8 17,1*	9,5 15,0*	12,3 15,0*	7,5 13,4*	9,8 13,4*	6,0	8,0 12,0*					4,8 9,1*	6,6 9,1*	49'10"
15	Stabilizers raised 4 pt. outriggers down	32,3 34,2*	34,2* 34.2*	21,0 25,9*	25,9* 25.9*	15,1 21.0*	19,7 21,0*	11,5 17,7*	14,9 17.7*	9,0 15.4*	11,8 15,4*	7,2 13,6*	9,5 13,6*	5,8 12,0*	7,8 12,0*	4,7 10,4*	6,4 10,4*			4,6 9,2*	6,3 9,2*	50' 8"
10	Stabilizers raised 4 pt. outriggers down	27,6 31,4*	31,4* 31.4*	18,7 27.6*	25,2 27.6*	13,8 22,0*	18,3 22,0*	10,6	14,1 18,3*	8,4 15,7*	11,2 15,7*	6,8	9,1 13,7*	5,6 12,0*	7,6 12,0*	4,6 10,1*	6,3 10,1*			4,4 9,4*	6,1 9,4*	51' 1"
5	Stabilizers raised 4 pt. outriggers down	11,0* 11,0*	11,0* 11,0*	16,8 28.6*	23,0 28.6*	12,6 22.6*	17,0 22,6*	9,8 18.6*	13,3 18.6*	7,9 15.8*	10,7 15,8*	6,5 13.6*	8,8 13,6*	5,3 11.7*	7,3 11,7*	4,5 9,6*	6,2 9,6*			4,3 8,9*	6,0 8,9*	51'
0	Stabilizers raised 4 pt. outriggers down	9,7* 9,7*	9,7* 9,7*	15,4 25,7*	21,6 25,7*	11,7 22,5*	16,1 22,5*	9,2 18,5*	12,6 18,5*	7,5 15,6*	10,2 15,6*	6,2	8,5 13,2*	5,2 11,1*	7,2 11,1*	4,4 8.4*	6,2 8.4*			4,4 8.1*	6,1 8,1*	50' 5"
- 5	Stabilizers raised 4 pt. outriggers down	11,1* 11,1*	11,1* 11.1*	14,7 22,2*	20,8 22,2*	11,1 21.4*	15,4 21,4*	8,8 17,7*	12,1 17.7*	7,2 14,8*	9,9 14,8*	6,0 12,4*	8,3 12,4*	5,1 10.0*	7,0 10,0*	0,4	0,4			4,6 8.2*	6,5 8,2*	48'
-10	Stabilizers raised 4 pt. outriggers down	11,1	11,1	14,5 22,5*	20,6 22,5*	10,8 19.0*	15,1 19.0*	8,5 15.9*	17,7 11,9 15,9*	7,0 13,2*	9,7 13,2*	5,9 10.7*	8,2 10,7*	10,0	10,0					5,4 9.3*	7,5 9.3*	42'10"
-15	Stabilizers raised 4 pt. outriggers down			22,5	22,3	17,0	17,0	13,7	10,7	13,2	10,2	10,7	10,7							7,0	7,3	

Height Gan be slewed through 360° In longitudinal position of undercarriage


Max. reach

* Limited by hydr. capacity


The lift capacities on the stick end without attachment are stated in lb x 1,000 and are valid on a firm, level supporting surface with blocked oscillating axle. These capacities can be slewed through 360° with the undercarriage in the transverse position. Capacities in the longitudinal position of the undercarriage (±15°) are specified over the steering axle with the stabilizers raised and over the rigid axle with the stabilizers down. Indicated loads based on the ISO 10567 standard and do not exceed 75% of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. This operating temperature is ensured by continuous movement of the boom. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capability of the hydraulic elements, or the maximum permissible lifting capacity of the load hook.

LH 50 M - Equipment GA17

Industry - Kinematic 2A



Dimensions



Operating weight

The operating weight includes the basic machine with 4 point outriggers, hydr. cab elevation, 4 solid tires, straight boom 31'6", angled stick 247" and multi-tine grab GMM 50-5/1.18 yd³ semiclosed tines.

Weight	97.400 lb

1		15	ift	20 ft		25	ft	30)ft	35	ift	40	ft	45	ft	50	ft	55 ft				7
16/			P		P		P		P		P		P		P		P		P		₽ .	ĺ
ft	Undercarriage	⊶	밥	⊶ 5⊃	밤	− 5	빤	⊶ 5	밤	− ₹	반	⊶5)	밤	⊶ 5	밤	-5)	빤	⊶ □	밤	⊶ 5	반	ft in
60	Stabilizers raised 4 pt. outriggers down																			15,4* 15,4*	15,4* 15,4*	18' 5"
55	Stabilizers raised 4 pt. outriggers down					15,0* 15,0*	15,0* 15,0*													11,7* 11,7*	11,7* 11,7*	28'11"
50	Stabilizers raised 4 pt. outriggers down					16,9* 16,9*	16,9* 16,9*	13,6 14,8*	14,8* 14,8*	10,0 11,1*	11,1* 11,1*									9,5 10,1*	10,1* 10,1*	35'10"
45	Stabilizers raised 4 pt. outriggers down							14,0 15,3*	15,3* 15,3*	10,5 13,8*	13,4 13,8*	7,9 10,5*	10,2 10,5*							7,4 9,3*	9,3* 9,3*	40'11"
40	Stabilizers raised 4 pt. outriggers down							14,1 15,1*	15,1* 15,1*	10,7 13,6*	13,5 13,6*	8,2 12,4*	10,5 12,4*							6,2 8,7*	8,2 8,7*	44'11"
35	Stabilizers raised 4 pt. outriggers down							14,0 15,2*	15,2* 15,2*	10,6 13,6*	13,5 13,6*	8,2 12,4*	10,6 12,4*	6,3 11,4*	8,4 11,4*					5,3 8,4*	7,2 8,4*	48' 1"
30	Stabilizers raised 4 pt. outriggers down					17,6* 17,6*	17,6* 17,6*	13,6 15,4*	15,4* 15,4*	10,4 13,8*	13,3 13,8*	8,1 12,4*	10,4 12,4*	6,3 11,3*	8,3 11,3*	4,9 9,1*	6,6 9,1*			4,7 8,2*	6,5 8,2*	50' 6"
25	Stabilizers raised 4 pt. outriggers down					17,7 18,3*	18,3* 18,3*	13,1 15,8*	15,8* 15,8*	10,0 14,0*	12,9 14,0*	7,8 12,6*	10,2 12,6*	6,2 11,4*	8,2 11,4*	4,9 10,3*	6,6 10,3*			4,3 8,1*	6,0 8,1*	52' 5"
20	Stabilizers raised 4 pt. outriggers down			22,9* 22,9*	22,9* 22,9*	16,5 19,2*	19,2* 19,2*	12,3 16,4*	15,9 16,4*	9,5 14,4*	12,3 14,4*	7,5 12,8*	9,8 12,8*	6,0 11,5*	8,0 11,5*	4,8 10,3*	6,5 10,3*			4,0 8,1*	5,6 8,1*	53' 8"
15	Stabilizers raised 4 pt. outriggers down	32,7 33,0*	33,0* 33,0*	21,2 25,0*	25,0* 25,0*	15,1 20,2*	19,7 20,2*	11,4 17,0*	14,9 17,0*	8,9 14,7*	11,7 14,7*	7,1 13,0*	9,4 13,0*	5,7 11,6*	7,7 11,6*	4,6 10,3*	6,4 10,3*			3,8 8,1*	5,4 8,1*	54' 7"
10	Stabilizers raised 4 pt. outriggers down	27,5 33,3*	33,3* 33,3*	18,6 26,7*	25,1 26,7*	13,6 21,2*	18,2 21,2*	10,5 17,6*	13,9 17,6*	8,3 15,1*	11,1 15,1*	6,6 13,1*	9,0 13,1*	5,4 11,6*	7,4 11,6*	4,4 10,2*	6,2 10,2*			3,6 8,3*	5,2 8,3*	54'11"
5	Stabilizers raised 4 pt. outriggers down	9,6* 9,6*	9,6* 9,6*	16,4 27,7*	22,6 27,7*	12,3 21,8*	16,7 21,8*	9,6 18,0*	13,0 18,0*	7,7 15,3*	10,4 15,3*	6,2 13,2*	8,6 13,2*	5,1 11,5*	7,1 11,5*	4,3 9,9*	6,0 9,9*			3,6 7,9*	5,2 7,9*	54'10"
0	Stabilizers raised 4 pt. outriggers down	8,2* 8,2*	8,2* 8,2*	14,8 21,5*	21,0 21,5*	11,2 21,9*	15,6 21,9*	8,9 18,0*	12,2 18,0*	7,2 15,2*	9,9 15,2*	5,9 13,0*	8,2 13,0*	4,9 11,1*	6,9 11,1*	4,1 9,3*	5,9 9,3*			3,6 7,2*	5,2 7,2*	54' 4"
- 5	Stabilizers raised 4 pt. outriggers down	9,2* 9,2*	9,2* 9,2*	14,0 18,3*	18,3* 18,3*	10,5 21,1*	14,9 21,1*	8,3 17,4*	11,7 17,4*	6,8 14,6*	9,5 14,6*	5,6 12,4*	7,9 12,4*	4,7 10,4*	6,7 10,4*	4,0 8,4*	5,8 8,4*			3,8 7,0*	5,4 7,0*	52' 6"
-10	Stabilizers raised 4 pt. outriggers down			13,6 18,4*	18,4* 18,4*	10,1 19,2*	14,5 19,2*	8,0 16,1*	11,4 16,1*	6,5 13,5*	9,3 13,5*	5,5 11,3*	7,7 11,3*	4,6 9,2*	6,6 9,2*					4,2 7,7*	6,1 7,7*	48' 1"
-15	Stabilizers raised 4 pt. outriggers down					10,0 16,1*	14,3 16,1*	7,9 13,7*	11,2 13,7*	6,5 11,5*	9,2 11,5*									5,5 9,7*	7,9 9,7*	39' 4"
		•																				


Height Scan be slewed through 360° In longitudinal position of undercarriage Max. reach * Limited by hydr. capacity

The lift capacities on the stick end without attachment are stated in lb x 1,000 and are valid on a firm, level supporting surface with blocked oscillating axle. These ca


The lift capacities on the stick end without attachment are stated in lb x 1,000 and are valid on a firm, level supporting surface with blocked oscillating axle. These capacities can be slewed through 360° with the undercarriage in the transverse position. Capacities in the longitudinal position of the undercarriage (±15°) are specified over the steering axle with the stabilizers raised and over the rigid axle with the stabilizers down. Indicated loads based on the ISO 10567 standard and do not exceed 75% of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. This operating temperature is ensured by continuous movement of the boom. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capability of the hydraulic elements, or the maximum permissible lifting capacity of the load hook.

LH 50 M - Equipment GA18

Industry - Kinematic 2A



Dimensions



Operating weight

The operating weight includes the basic machine with 4 point outriggers, hydr. cab elevation, 4 solid tires, straight boom 34^9 °, angled stick 26'3° and multi-tine grab GM 65/0.78yd 3 semiclosed tines.

Weight	98.100 lb

16		15ft 20ft		ft 20 ft 25 ft				30	ft	35	ift	40	ft	45	ft	50	ft	55	ft	AB		
16/			P		P		P		P		P		P		P		P		P		P	Ĭ
ft	Undercarriage	− ∰		⊶ 5	밥	− ∰		-5	밤	− ∰		⊶	밤	₽		-£	밤	=	바	=	바	ft in
65	Stabilizers raised 4 pt. outriggers down																			14,5* 14,5*	14,5* 14,5*	16'11"
60	Stabilizers raised 4 pt. outriggers down					13,4* 13,4*	13,4* 13,4*													10,8* 10,8*	10,8* 10,8*	28'11"
55	Stabilizers raised 4 pt. outriggers down					15,3* 15,3*	15,3* 15,3*	13,4* 13,4*	13,4* 13,4*	10,0 10,6*	10,6* 10,6*									9,1 9,3*	9,3* 9,3*	36' 6"
50	Stabilizers raised 4 pt. outriggers down							14,2 14,6*	14,6* 14,6*	10,6 12,9*	12,9* 12,9*	7,9 10,4*	10,3 10,4*							6,9 8,5*	8,5* 8,5*	42' 1"
45	Stabilizers raised 4 pt. outriggers down							14,4 14,4*	14,4* 14,4*	10,8 12,7*	12,7* 12,7*	8,2 11,4*	10,6 11,4*	6,1 9,6*	8,2 9,6*					5,5 8,0*	7,5 8,0*	46' 7"
40	Stabilizers raised 4 pt. outriggers down							14,3 14,4*	14,4* 14,4*	10,8 12,7*	12,7* 12,7*	8,2 11,4*	10,6 11,4*	6,3 10,3*	8,3 10,3*	4,6 7,8*	6,4 7,8*			4,6 7,7*	6,4 7,7*	50' 1"
35	Stabilizers raised 4 pt. outriggers down							14,0 14,5*	14,5* 14,5*	10,5 12,8*	12,8* 12,8*	8,1 11,4*	10,5 11,4*	6,2 10,3*	8,3 10,3*	4,7 9,4*	6,5 9,4*			4,0 7,4*	5,6 7,4*	53'
30	Stabilizers raised 4 pt. outriggers down					17,2* 17,2*	17,2* 17,2*	13,5 14,8*	14,8* 14,8*	10,2 12,9*	12,9* 12,9*	7,8 11,5*	10,2 11,5*	6,1 10,3*	8,1 10,3*	4,7 9,4*	6,5 9,4*	3,5 7,6*	5,1 7,6*	3,5 7,3*	5,0 7,3*	55' 2"
25	Stabilizers raised 4 pt. outriggers down					17,3 17,8*	17,8* 17,8*	12,7 15,1*	15,1* 15,1*	9,6 13,1*	12,5 13,1*	7,4 11,6*	9,8 11,6*	5,8 10,4*	7,8 10,4*	4,5 9,4*	6,3 9,4*	3,5 8,4*	5,1 8,4*	3,1 7,3*	4,6 7,3*	56'11"
20	Stabilizers raised 4 pt. outriggers down	21,1* 21,1*	21,1* 21,1*	22,7 22,8*	22,8* 22,8*	15,8 18,5*	18,5* 18,5*	11,7 15.6*	15,3 15,6*	8,9 13,4*	11,8 13,4*	7,0 11,8*	9,3 11,8*	5,5 10,5*	7,5 10,5*	4,3 9,4*	6,1 9,4*	3,4 8,4*	4,9 8,4*	2,8 7,3*	4,3 7,3*	58' 1"
15	Stabilizers raised 4 pt. outriggers down	30,2 32,5*	32,5* 32,5*	19,7 24,2*	24,2* 24,2*	14,1 19,3*	18,7 19,3*	10,6 16,0*	14,1 16,0*	8,2 13,7*	11,0 13,7*	6,4 12,0*	8,8 12,0*	5,1 10,6*	7,1 10,6*	4,1 9,4*	5,8 9,4*	3,2 8,3*	4,8 8,3*	2,6 7,3*	4,1 7,3*	58'11"
10	Stabilizers raised 4 pt. outriggers down	13,0* 13,0*	13,0* 13,0*	16,6 25,3*	23,0 25,3*	12,3 19.9*	16,8 19.9*	9,4 16,4*	12,9 16,4*	7,4 13,9*	10,2 13,9*	5,9 12,1*	8,2 12,1*	4,7 10,6*	6,7 10,6*	3,8 9,3*	5,6 9,3*	3,1 8,1*	4,6 8,1*	2,5 6,9*	4,0 6,9*	59' 2"
5	Stabilizers raised 4 pt. outriggers down	6,2* 6,2*	6,2* 6,2*	14,1 21,1*	20,3 21,1*	10,7 20,2*	15,1 20,2*	8,4 16,6*	11,8 16,6*	6,7 14,0*	9,4 14,0*	5,4 12,1*	7,7 12,1*	4,4 10,5*	6,4 10,5*	3,6 9,1*	5,3 9,1*	2,9 7,8*	4,5 7,8*	2,4 6,5*	3,9 6,5*	59' 2"
0	Stabilizers raised 4 pt. outriggers down	5,9* 5.9*	5,9* 5.9*	12,4 14.2*	14,2* 14.2*	9,5 20.0*	13,8 20.0*	7,5 16.5*	10,9 16.5*	6,1 13.9*	8,8 13.9*	4,9 11.9*	7,2 11,9*	4,1 10.2*	6,0 10.2*	3,3 8,8*	5,1 8.8*	2,8 7.3*	4,3 7,3*	2,4 5,9*	3,9 5.9*	58' 8"
- 5	Stabilizers raised 4 pt. outriggers down	7,0* 7.0*	7,0* 7.0*	11,5	13,1* 13.1*	8,7 19.1*	13,0 19.1*	6,9 15,8*	10,3 10,2 15,8*	5,6 13,3*	8,3 13,3*	4,6 11,4*	6,9 11.4*	3,8 9,7*	5,8 9,7*	3,2 8,2*	4,9 8,2*	2,7	4,2 6.5*	2,5 5,2*	4,0 5,2*	57' 8"
-10	Stabilizers raised 4 pt. outriggers down	7,0	7,0	11,2 13.6*	13,6* 13.6*	8,3 17,2*	12,5 17,2*	6,5 14,6*	9,8 14,6*	5,3 12,4*	8,0 12,4*	4,4 10,5*	6,6 10,5*	3,6 8.8*	5,6 8,8*	3,1 7,2*	4,8 7.2*	0,0	0,0	2,7 5.7*	4,3 5,7*	53'10"
-15	Stabilizers raised 4 pt. outriggers down			13,0	10,0	8,2 14,5*	12,4 14,5*	6,3	9,7 12,6*	5,1 10,7*	7,8 10,7*	4,2 9,0*	6,5 9,0*	3,6 7,4*	5,6 7,4*	7,2	7,2			3,4 6,7*	5,2 6,7*	46'11"

Height Gan be slewed through 360° In longitudinal position of undercarriage


Max. reach

* Limited by hydr. capacity

The lift capacities on the stick end without attachment are stated in lb x 1,000 and are valid on a firm, level supporting surface with blocked oscillating axle. These capacities can be slewed through 360° with the undercarriage in the transverse position. Capacities in the longitudinal position of the undercarriage (±15°) are specified over the steering axle with the stabilizers raised and over the rigid axle with the stabilizers down. Indicated loads based on the ISO 10567 standard and do not exceed 75% of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. This operating temperature is ensured by continuous movement of the boom. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capability of the hydraulic elements, or the maximum permissible lifting capacity of the load hook.

LH 50 M - Equipment AF16

Industry - Kinematic 2D




16		15	ft	20) ft	25	ift	30	ft	35	ft	40	ft	45	ft	50	ft	55	ft	-	~£	<u>⊃</u>
12/			P		P		P		P		P		P		P		P		₽ '	i	₽ Ì	ĺ
ft	Undercarriage	□		-5	반	□=	바	-5	밥	□=		-47	밥	–	발	-5	바	-5	반	⊶ 5	밥	ft in
60	Stabilizers raised																					
	4 pt. outriggers down Stabilizers raised					11,3*	11,3*													10.9*	10,9*	
55	4 pt. outriggers down					11,3*	11,3*													10,9*	10,9*	25' 5"
50	Stabilizers raised 4 pt. outriggers down							11,9* 11,9*	11,9* 11.9*											9,5* 9,5*	9,5* 9,5*	33' 1"
45	Stabilizers raised							13,2*	13,2*	10,9	11,7*									8,8*	8,8*	38' 7"
	4 pt. outriggers down Stabilizers raised							13,2* 13,0*	13,2* 13,0*	11,7* 11.1	11,7* 11.9*	8.4	10.9							8,8* 7,2	8,8* 8,4*	
40	4 pt. outriggers down							13,0*	13,0*	11,9*	11,9*	11,0*	11,0*							8,4*	8,4*	42'10"
35	Stabilizers raised 4 pt. outriggers down							13,1* 13,1*	13,1* 13,1*	11,0 11.9*	11,9* 11.9*	8,5 10.9*	10,9 10.9*	6,5 9.4*	8,6 9.4*					6,1 8.2*	8,1 8,2*	46' 1"
70	Stabilizers raised							13,3*	13,3*	10.8	12,0*	8.3	10,9	6.5	8,5					5,3	7,2	(0) 00
30	4 pt. outriggers down							13,3*	13,3*	12,0*	12,0*	11,0*	11,0*	10,2*	10,2*					8,1*	8,1*	48' 8"
25	Stabilizers raised 4 pt. outriggers down							13,6 13.8*	13,8* 13,8*	10,4 12.3*	12,3* 12,3*	8,1 11.2*	10,5 11.2*	6,3 10.2*	8,4 10.2*	4,9 8.9*	6,7 8.9*			4,8 8.1*	6,5 8.1*	50' 7"
20	Stabilizers raised					16,7*	16,7*	12,8	14,4*	9,8	12,7	7,7	10,1	6,1	8,1	4,8	6,6			4,4	6,1	52'
20	4 pt. outriggers down	00.0*	00.0*	07.0*	07.0*	16,7*	16,7*	14,4*	14,4*	12,7*	12,7*	11,4*	11,4*	10,4*	10,4*	9,5*	9,5*			8,2*	8,2*	32
15	Stabilizers raised 4 pt. outriggers down	28,8* 28,8*	28,8* 28,8*	21,9* 21,9*	21,9* 21,9*	15,7 17,8*	17,8* 17,8*	11,8 15,1*	15,1* 15,1*	9,1 13,2*	12,0 13,2*	7,2 11,7*	9,6 11,7*	5,8 10,6*	7,8 10,6*	4,6 9,6*	6,4 9,6*			4,1 8,3*	5,7 8,3*	52'10"
10	Stabilizers raised	28,3	32,5*	19,1	23,8*	14,0	18,6	10,7	14,2	8,5	11,3	6,8	9,1	5,5	7,5	4,4	6,2			3,9	5,5	53' 2"
	4 pt. outriggers down Stabilizers raised	32,5* 15,3*	32,5* 15,3*	23,8* 16,7	23,8* 23,0	18,9* 12,5	18,9* 17,0	15,8* 9,7	15,8* 13,2	13,6* 7.8	13,6* 10,6	12,0*	12,0* 8.6	10,7* 5,1	10,7* 7,2	9,6* 4,2	9,6* 6,0			8,6* 3,7	8,6* 5,4	
5	4 pt. outriggers down	15,3*	15,3*	25,4*	25,4*	19,9*	19,9*	16,4*	16,4*	14,0*	14,0*	12,2*	12,2*	10,8*	10,8*	9,6*	9,6*			8,8*	8,8*	53' 1"
0	Stabilizers raised	11,9*	11,9*	14,9	21,1	11,3	15,7	8,9	12,3	7,2	10,0	5,9	8,2	4,9	6,9	4,0	5,8			3,7	5,3	52' 7"
_	4 pt. outriggers down Stabilizers raised	11,9* 12.0*	11,9* 12,0*	26,1* 13,8	26,1* 19.9	20,5* 10.4	20,5* 14.8	16,8* 8.3	16,8* 11.6	14,3* 6.7	14,3* 9,5	12,3* 5.5	12,3* 7.9	10,8*	10,8*	9,4* 3.9	9,4* 5,7			8,6* 3,7	8,6* 5,4	
- 5	4 pt. outriggers down	12,0*	12,0*	21,5*	21,5*	20,5*	20,5*	16,8*	16,8*	14,2*	14,2*	12,2*	12,2*	10,5*	10,5*	8,9*	8,9*			8,4*	8,4*	51' 6"
-10	Stabilizers raised 4 pt. outriggers down	13,0* 13.0*	13,0* 13.0*	13,2 20,5*	19,3 20,5*	9,9 19,8*	14,3 19,8*	7,8 16,4*	11,2 16,4*	6,4 13,8*	9,1 13,8*	5,3 11,7*	7,6 11,7*	4,5 9.9*	6,5 9,9*					3,9 8.0*	5,6 8,0*	49'11"
-15	Stabilizers raised	10,0	10,0	13,1	19,1	9,7	14,0	7,6	11,0	6,2	9,0	5,2	7,5	4,4	6,4					4,2	6,1	47' 1"
- 13	4 pt. outriggers down			20,9*	20,9*	18,2*	18,2*	15,2*	15,2*	12,8*	12,8*	10,7*	10,7*	8,7*	8,7*					7,8*	7,8*	4/ 1
-20	Stabilizers raised 4 pt. outriggers down							7,6 13,2*	11,0 13,2*	6,2 11,0*	9,0 11,0*									5,9 10,3*	8,4 10,3*	36' 7"

Height 🖰 Can be slewed through 360° 🖟 In longitudinal position of undercarriage 🧼 Max. reach * Limited by hydr. capacity


The lift capacities on the stick end without attachment are stated in lb x 1,000 and are valid on a firm, level supporting surface with blocked oscillating axle. These capacities can be slewed through 360° with the undercarriage in the transverse position. Capacities in the longitudinal position of the undercarriage (±15°) are specified over the steering axle with the stabilizers raised and over the rigid axle with the stabilizers down. Indicated loads based on the ISO 10567 standard and do not exceed 75% of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. This operating temperature is ensured by continuous movement of the boom. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capability of the hydraulic elements, or the maximum permissible lifting capacity of the load hook.

LH 50 M - Equipment GA13

Industry - Kinematic 2A



Dimensions



Operating weight

The operating weight includes the basic machine with 4 point outriggers, hydr. cab elevation, 4 pneumatic tires, straight boom 24'11", angled stick 19'8" and wood grab GMH 40 / 2.27 yd2.

92,800lb


16		15	tt	20	itt	25	ft	30)ft	35	ft	40) ft	45	ft	50	ft	55	ft		<u>~</u> ₫	
12/			P		P		P		P		P		P		P		P		P		P	ا
ft	Undercarriage			-5	반			-5	반				반	-€	ď	-€	반		반		반	ft in
50	Stabilizers raised 4 pt. outriggers down																			21,1* 21,1*	21,1* 21,1*	12' 8"
45	Stabilizers raised 4 pt. outriggers down			19,3* 19,3*	19,3* 19,3*															14,7* 14,7*	14,7* 14,7*	23' 7"
40	Stabilizers raised 4 pt. outriggers down			21,9* 21,9*	21,9* 21,9*	17,1 18,9*	18,9* 18,9*	12,4 12,7*	12,7* 12,7*											12,3 12,6*	12,6* 12,6*	30' 1"
35	Stabilizers raised 4 pt. outriggers down					17,4 19,5*	19,5* 19,5*	12,8 17,8*	16,2 17,8*											9,8 11,6*	11,6* 11,6*	34' 7"
30	Stabilizers raised 4 pt. outriggers down					17,4 19,5*	19,5* 19,5*	12,8 17,6*	16,3 17,6*	9,8 16,2*	12,5 16,2*									8,3 11,0*	10,7 11,0*	38'
25	Stabilizers raised 4 pt. outriggers down			22,9* 22,9*	22,9* 22,9*	17,0 20,0*	20,0* 20,0*	12,6 17,9*	16,0 17,9*	9,7 16,2*	12,4 16,2*	7,5 11,8*	9,8 11,8*							7,4 10,7*	9,6 10,7*	40' 5"
20	Stabilizers raised 4 pt. outriggers down			23,1 24,5*	24,5* 24,5*	16,3 20,9*	20,8 20,9*	12,2 18,4*	15,6 18,4*	9,5 16,4*	12,2 16,4*	7,5 14,8*	9,7 14,8*							6,8 10,6*	8,9 10,6*	42' 1"
15	Stabilizers raised 4 pt. outriggers down	33,5 33,9*	33,9* 33,9*	21,6 26,6*	26,6* 26,6*	15,5 22,1*	19,9 22,1*	11,7 19,0*	15,1 19,0*	9,2 16,7*	11,9 16,7*	7,3 14,8*	9,6 14,8*							6,4 10,6*	8,4 10,6*	43' 2"
10	Stabilizers raised 4 pt. outriggers down	29,9 38,4*	38,4* 38,4*	19,9 28,8*	26,1 28,8*	14,5 23,3*	18,9 23,3*	11,1 19,7*	14,4 19,7*	8,8 17,0*	11,5 17,0*	7,2 14,7*	9,4 14,7*							6,2 10,8*	8,2 10,8*	43' 8"
5	Stabilizers raised 4 pt. outriggers down	26,9 33,8*	33,8* 33,8*	18,3 30,5*	24,4 30,5*	13,6 24,2*	17,9 24,2*	10,6 20,0*	13,9 20,0*	8,5 17,0*	11,1 17,0*	7,0 14,3*	9,2 14,3*							6,1 11,3*	8,1 11,3*	43' 6"
0	Stabilizers raised 4 pt. outriggers down	21,3* 21,3*	21,3* 21,3*	17,2 30,7*	23,2 30,7*	12,9 24,2*	17,1 24,2*	10,1 19,9*	13,4 19,9*	8,2 16,5*	10,9 16,5*	6,8 13,3*	9,0 13,3*							6,2 10,8*	8,3 10,8*	42'11"
- 5	Stabilizers raised 4 pt. outriggers down	20,8* 20,8*	20,8* 20,8*	16,6 28,8*	22,6 28,8*	12,4 23,0*	16,6 23,0*	9,8 18,7*	13,1 18,7*	8,0 15,1*	10,7 15,1*									6,8 11,4*	9,1 11,4*	39' 8"
-10	Stabilizers raised 4 pt. outriggers down			16,4 24,4*	22,4 24,4*	12,2 19,9*	16,5 19,9*	9,7 16,0*	13,0 16,0*											8,9 14,4*	11,9 14,4*	32' 1"

Max. reach * Limited by hydr. capacity The lift capacities on the stick end without attachment are stated in lb x 1,000 and are valid on a firm, level supporting surface with blocked oscillating axle. These capacities can be slewed through 360° with the undercarriage in the transverse position. Capacities in the longitudinal position of the undercarriage (±15°) are specified over the steering axle with the stabilizers raised and over the rigid axle with the stabilizers down. Indicated loads based on the ISO 10567 standard and do not exceed 75% of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. This operating temperature is ensured by continuous movement of the boom. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capability of the hydraulic elements, or the maximum permissible lifting capacity of the load hook.


Height 🖰 Can be slewed through 360° 🖺 In longitudinal position of undercarriage

LH 50 M - Equipment GKG14

Industry - Kinematic 2A



Dimensions



Operating weight

The operating weight includes the basic machine with 4 point outriggers, hydr. cab elevation, 4 solid tires, straight boom 24'11", stick 19' with counterstay and wood grab 0.84 yd².

Weight	95,700 lb


16		15	ift	20) ft	25	ft	30)ft	35	ft	40	ft	45	ift	50	ft	55	ft	-	~ <u>d</u>	⊃
12/			P		P		P		P		P		P		P		P		P		Π.	ĺ
ft	Undercarriage	-5		-5	반	-		-5	造			-47	반	-5		-€	빤	-5	반	-5	밥	ft in
50	Stabilizers raised 4 pt. outriggers down			15,7* 15,7*	15,7* 15,7*															13,0* 13,0*	13,0* 13,0*	22' 5"
45	Stabilizers raised 4 pt. outriggers down					15,5* 15,5*	15,5* 15,5*													10,5* 10,5*	10,5* 10,5*	30'
40	Stabilizers raised 4 pt. outriggers down					17,3* 17,3*	17,3* 17,3*	12,8 14,8*	14,8* 14,8*	9,3 9,6*	9,6* 9,6*									9,1 9,2*	9,2* 9,2*	35' 2"
35	Stabilizers raised 4 pt. outriggers down					16,9* 16,9*	16,9* 16,9*	13,0 15,4*	15,4* 15,4*	9,6 13,7*	12,5 13,7*									7,4 8,5*	8,5* 8,5*	39' 2"
30	Stabilizers raised 4 pt. outriggers down					16,9* 16,9*	16,9* 16,9*	13,0 15,3*	15,3* 15,3*	9,7 14,0*	12,5 14,0*	7,3 11,6*	9,6 11,6*							6,4 8,1*	8,1* 8,1*	42' 2"
25	Stabilizers raised 4 pt. outriggers down					17,4* 17,4*	17,4* 17,4*	12,7 15,6*	15,6* 15,6*	9,5 14,1*	12,4 14,1*	7,2 13,0*	9,6 13,0*							5,6 7,8*	7,7 7,8*	44' 5"
20	Stabilizers raised 4 pt. outriggers down					16,7 18,2*	18,2* 18,2*	12,2 16,1*	15,8 16,1*	9,2 14,4*	12,0 14,4*	7,1 13,1*	9,4 13,1*	5,4 9,8*	7,4 9,8*					5,2 7,7*	7,1 7,7*	45'11"
15	Stabilizers raised 4 pt. outriggers down			22,6 23,1*	23,1* 23,1*	15,7 19,4*	19,4* 19,4*	11,6 16,8*	15,1 16,8*	8,8 14,8*	11,6 14,8*	6,8 13,2*	9,2 13,2*	5,3 11,7*	7,3 11,7*					4,8 7,7*	6,7 7,7*	46'11"
10	Stabilizers raised 4 pt. outriggers down	32,2 33,4*	33,4* 33,4*	20,6 25,5*	25,5* 25,5*	14,6 20,8*	19,1 20,8*	10,8 17,6*	14,3 17,6*	8,3 15,2*	11,1 15,2*	6,5 13,3*	8,9 13,3*	5,2 11,5*	7,2 11,5*					4,7 7,9*	6,5 7,9*	47' 5"
5	Stabilizers raised 4 pt. outriggers down	28,1 37,6*	37,6* 37,6*	18,6 27,7*	25,0 27,7*	13,4 22,0*	17,9 22,0*	10,1 18,2*	13,5 18,2*	7,9 15,5*	10,6 15,5*	6,2 13,3*	8,6 13,3*	5,0 11,1*	7,0 11,1*					4,6 8,1*	6,5 8,1*	47' 4"
0	Stabilizers raised 4 pt. outriggers down	25,2 28,4*	28,4* 28,4*	16,9 28,9*	23,2 28,9*	12,4 22,6*	16,8 22,6*	9,5 18,5*	12,9 18,5*	7,4 15,5*	10,2 15,5*	6,0 12,9*	8,3 12,9*	4,9 10,1*	6,9 10,1*					4,6 8,5*	6,5 8,5*	46' 7"
- 5	Stabilizers raised 4 pt. outriggers down	21,3* 21,3*	21,3* 21,3*	15,8 28,5*	22,0 28,5*	11,6 22,3*	16,0 22,3*	9,0 18,1*	12,4 18,1*	7,1 14,8*	9,9 14,8*	5,8 11,9*	8,1 11,9*							5,0 8,7*	7,0 8,7*	44' 5"
-10	Stabilizers raised 4 pt. outriggers down	21,3* 21,3*	21,3* 21,3*	15,3 26,0*	21,4 26,0*	11,2 20,6*	15,6 20,6*	8,7 16,5*	12,1 16,5*	7,0 13,1*	9,7 13,1*									5,8 9,9*	8,2 9,9*	39' 7"

Height — Can be slewed through 360° In longitudinal position of undercarriage Max. reach * Limited by hydr. capacity


The lift capacities on the stick end without attachment are stated in lb x 1,000 and are valid on a firm, level supporting surface with blocked oscillating axle. These capacities can be slewed through 360° with the undercarriage in the transverse position. Capacities in the longitudinal position of the undercarriage (±15°) are specified over the steering axle with the stabilizers raised and over the rigid axle with the stabilizers down. Indicated loads based on the ISO 10567 standard and do not exceed 75% of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. This operating temperature is ensured by continuous movement of the boom. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capability of the hydraulic elements, or the maximum permissible lifting capacity of the load hook.

LH 40 C - Equipment GA14

Industry - Kinematic 2A



Dimensions



Operating weight and ground pressure

The operating weight includes the basic machine with rigid cab elevation, straight boom 28'3". angled stick 19'8" and multi-tine grab GMM 50-5/1.18 yd³ semi-closed tines.

Weight	88,400 lb
Pad width	24"
Ground pressure	on request


1		15	ift	20	ft	25	ft	30	ft	35	ft	40)ft	45	ift	50	ft	55	ft	-	~ ₫	2
12/			4		-		4		-1		9		3		9		J.		1			<u> </u>
ft	Undercarriage	− 4				- <u>-</u>		-47		-	135	-47			25	€				−₽		ft in
55	EW																					
50	EW	21,2*	21,2*																	17,6*	17,6*	18' 4"
45	EW			20,8*	20,8*	17,0*	17,0*													13,9*	13,9*	27' 4"
40	EW					18,0*	18,0*	16,0*	16,0*											12,3*	12,3*	33' 2"
35	EW					17,8*	17,8*	15,7*	15,7*	14,2*	14,2*									11,4*	11,4*	37' 7"
30	EW					17,9*	17,9*	15,7*	15,7*	14,1*	14,1*	12,6	12,7*							10,9*	10,9*	40'11"
25	EW				21,7*	18,3*	18,3*	16,0*	16,0*	14,2*	14,2*	12,6	12,7*							10,7*	10,7*	43' 4"
20	EW	27,2*	27,2*	22,9*	22,9*	19,0*	19,0*	16,4*	16,4*	14,4*	14,4*	12,4	12,7*	10,1	10,8*					10,1	10,6*	45' 1"
15	EW	32,2*	32,2*	24,5*	24,5*	19,9*	19,9*	16,8*	16,8*	14,6*	14,6*	12,2	12,8*	10,0	11,0*					9,6	10,5*	46' 2"
10	EW	35,2*	35,2*	26,0*	26,0*	20,7*	20,7*	17,2*	17,2*	14,5	14,7*	11,9	12,7*	9,9	10,8*					9,3	9,9*	46'10"
5	EW	13,6*	13,6*	26,7*	26,7*	21,1*	21,1*	17,4*	17,4*	14,1	14,7*	11,6	12,5*	9,8	10,3*					9,2*	9,2*	46'11"
0	EW	11,4*	11,4*	26,2*	26,2*	20,8*	20,8*	16,9	17,1*	13,7	14,2*	11,4	11,9*	9,3*	9,3*					8,3*	8,3*	46' 5"
- 5	EW	12,9*	12,9*	24,0*	24,0*	19,5*	19,5*	16,0*	16,0*	13,2*	13,2*	10,7*	10,7*							8,2*	8,2*	44' 1"
-10	EW			20,1*	20,1*	16,9*	16,9*	14,0*	14,0*	11,4*	11,4*									9,5*	9,5*	38' 5"
- 15	EW																					

Max. reach * Limited by hydr. capacity The lift capacities on the stick end without attachment are stated in lb x 1,000 and can be slewed through 360° on a firm, level supporting surface. Capacities are valid for 24" wide triple grouser pads (resp. flat pads). Indicated loads based on the ISO 10567 standard and do not exceed 75% of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. This operating temperature is ensured by continuous movement of the boom. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capability of the hydraulic elements, or the maximum permissible lifting capacity of the load hook.


Height 🖰 Can be slewed through 360° 🖟 In longitudinal position of undercarriage

LH 40 C - Equipment GA16

Industry - Kinematic 2A



Dimensions



Operating weight and ground pressure

The operating weight includes the basic machine with rigid cab elevation, straight boom 29°10", angled stick 22°4" and multi-tine grab GM 65 / 0.78 yd $^{\rm J}$ semi-closed tines.

Weight	88,400 lb
Pad width	24"
Ground pressure	on request


1		15	ft	20	ft	25	ft	30	ft	35	ft	40) ft	45	ft	50	ft	55	ft	-	~	-
10			1		1		1		1		1		J		ß		ſ		1			Ī
ft	Undercarriage	-41		50		− ∰				− ∰	<u> </u>	-41		− ∰	<u>, , , , , , , , , , , , , , , , , , , </u>	− ∰	٣	-5	100	−₽	٢	ft in
55	EW	19,0*	19,0*																	17,1*	17,1*	16'11"
50	EW			18,7*	18,7*	15,4*	15,4*													12,8*	12,8*	27' 5"
45	EW					17,3*	17,3*	15,3*	15,3*											11,1*	11,1*	34'
40	EW					16,9*	16,9*	14,9*	14,9*	13,4*	13,4*									10,2*	10,2*	38'11"
35	EW					16,8*	16,8*	14,8*	14,8*	13,2*	13,2*	12,0*	12,0*							9,7*	9,7*	42' 8"
30	EW					17,1*	17,1*	14,9*	14,9*	13,3*	13,3*	12,0*	12,0*	10,3	10,5*					9,3*	9,3*	45' 7"
25	EW			20,8*	20,8*	17,5*	17,5*	15,2*	15,2*	13,4*	13,4*	12,0*	12,0*	10,3	10,8*					9,1	9,2*	47'10"
20	EW			22,0*	22,0*	18,2*	18,2*	15,6*	15,6*	13,6*	13,6*	12,1*	12,1*	10,2	10,8*					8,5	9,1*	49' 5"
15	EW	30,8*	30,8*	23,5*	23,5*	19,0*	19,0*	16,1*	16,1*	13,9*	13,9*	12,1	12,2*	10,0	10,7*	8,3	9,2*			8,2	9,0*	50' 6"
10	EW	33,7*	33,7*	24,9*	24,9*	19,8*	19,8*	16,5*	16,5*	14,1*	14,1*	11,7	12,2*	9,7	10,6*	8,2	8,9*			7,9	8,5*	51'
5	EW	12,7*	12,7*	25,7*	25,7*	20,3*	20,3*	16,7*	16,7*	13,8	14,1*	11,3	12,1*	9,5	10,4*	8,1	8,4*			7,8	7,9*	51'
0	EW	9,7*	9,7*	25,4*	25,4*	20,1*	20,1*	16,5	16,5*	13,3	13,9*	11,0	11,8*	9,3	9,9*	7,5*	7,5*			7,1*	7,1*	50' 7"
- 5	EW	10,6*	10,6*	22,6*	22,6*	19,2*	19,2*	15,8*	15,8*	12,9	13,2*	10,8	11,0*	8,9*	8,9*					6,7*	6,7*	49'
-10	EW			20,6*	20,6*	17,2*	17,2*	14,3*	14,3*	11,9*	11,9*	9,7*	9,7*							7,5*	7,5*	44' 7"
-15	EW							11,8*	11,8*											10,3*	10,3*	33' 6"

Height — Can be slewed through 360° In longitudinal position of undercarriage — Max. reach * Limited by hydr. capacity


The lift capacities on the stick end without attachment are stated in lb x 1,000 and can be slewed through 360° on a firm, level supporting surface. Capacities are valid for 24" wide triple grouser pads (resp. flat pads). Indicated loads based on the ISO 10567 standard and do not exceed 75% of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. This operating temperature is ensured by continuous movement of the boom. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capability of the hydraulic elements, or the maximum permissible lifting capacity of the load hook.

LH 50 M HR - Equipment AF18

Industry - Kinematic 2C



Dimensions



Operating weight

The operating weight includes the basic machine with 4 point outriggers, turret 3'11", hydr. cab elevation, 4 solid tires, angled boom 31'6", flat angled stick 29'6" and grab for loose material GMZ $40/1.96\,yd^3$.


16		15	ft	20	ft	25	ft	30	ft	35	ift	40	ft	45	ft	50	ft	55	ft	-	~ @	<u>_</u>
12/			J		<u>_</u>		1		_		J		J		ď		Ĵ		J]	ĺ
ft	Undercarriage	− ∰				−₽	100				2	-4				- <u>-</u>				 □		ft in
65	4 pt. outriggers down																					
60	4 pt. outriggers down							10,1*	10,1*											8,6*	8,6*	32' 4"
55	4 pt. outriggers down									10,1*	10,1*									7,7*	7,7*	38'10"
50	4 pt. outriggers down									11,2*	11,2*	9,7*	9,7*							7,2*	7,2*	43'10"
45	4 pt. outriggers down									11,0*	11,0*	10,2*	10,2*	9,0*	9,0*					6,8*	6,8*	47' 8"
40	4 pt. outriggers down									11,0*	11,0*	10,2*	10,2*	9,5*	9,5*	7,5*	7,5*			6,6*	6,6*	50'11"
35	4 pt. outriggers down									11,2*	11,2*	10,2*	10,2*	9,5*	9,5*	8,9*	8,9*			6,5*	6,5*	53' 5"
30	4 pt. outriggers down									11,4*	11,4*	10,4*	10,4*	9,6*	9,6*	8,9*	8,9*	6,8*	6,8*	6,5*	6,5*	55' 4"
25	4 pt. outriggers down							13,2*	13,2*	11,8*	11,8*	10,7*	10,7*	9,8*	9,8*	9,0*	9,0*	8,3*	8,3*	6,5*	6,5*	56' 8"
20	4 pt. outriggers down					16,0*	16,0*	13,8*	13,8*	12,2*	12,2*	11,0*	11,0*	10,0*	10,0*	9,2*	9,2*	8,4*	8,4*	6,6*	6,6*	57' 7"
15	4 pt. outriggers down			21,1*	21,1*	17,2*	17,2*	14,6*	14,6*	12,7*	12,7*	11,3*	11,3*	10,2*	10,2*	9,3*	9,3*	8,5*	8,5*	6,8*	6,8*	58' 1"
10	4 pt. outriggers down	31,1*	31,1*	23,0*	23,0*	18,4*	18,4*	15,4*	15,4*	13,2*	13,2*	11,6*	11,6*	10,4*	10,4*	9,4*	9,4*	8,5*	8,5*	7,0*	7,0*	58' 2"
5	4 pt. outriggers down	20,2*	20,2*	24,6*	24,6*	19,4*	19,4*	16,0*	16,0*	13,7*	13,7*	11,9*	11,9*	10,6*	10,6*	9,4*	9,4*	8,4*	8,4*	7,3*	7,3*	57'10"
0	4 pt. outriggers down	13,7*	13,7*	25,6*	25,6*	20,1*	20,1*	16,5*	16,5*	14,0*	14,0*	12,1*	12,1*	10,6*	10,6*	9,4*	9,4*	8,2*	8,2*	7,6*	7,6*	57'
- 5	4 pt. outriggers down	12,8*	12,8*	23,1*	23,1*	20,2*	20,2*	16,6*	16,6*	14,0*	14,0*	12,1*	12,1*	10,5*	10,5*	9,1*	9,1*	7,6*	7,6*	7,4*	7,4*	55' 8"
-10	4 pt. outriggers down	13,2*	13,2*	21,0*	21,0*	19,8*	19,8*	16,3*	16,3*	13,7*	13,7*	11,8*	11,8*	10,1*	10,1*	8,5*	8,5*			7,0*	7,0*	54'
-15	4 pt. outriggers down	14,0*	14,0*	20,8*	20,8*	18,5*	18,5*	15,4*	15,4*	13,0*	13,0*	11,0*	11,0*	9,2*	9,2*	7,3*	7,3*			6,9*	6,9*	50'10"
- 20	4 pt. outriggers down					16,3*	16,3*	13,6*	13,6*	11,4*	11,4*	9,5*	9,5*							8,5*	8,5*	42' 7"
_																						

Height — Can be slewed through 360° In longitudinal position of undercarriage — Max. reach *Limited by hydr. capacity


The lift capacities on the stick end without attachment are stated in lb x 1,000 and are valid on a firm, level supporting surface with blocked oscillating axle. These capacities can be slewed through 360° with the undercarriage in the transverse position. Capacities in the longitudinal position of the undercarriage (=15°) are specified over the rigid axle with the stabilizers down. Indicated loads based on the ISO 10567 standard and do not exceed 75 % of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. This operating temperature is ensured by continuous movement of the boom. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capability of the hydraulic elements, or the maximum permissible lifting capacity of

LH 50 C HR - Equipment GA18

Industry - Kinematic 2A



Dimensions



Operating weight and ground pressure

The operating weight includes the basic machine with turret 67", hydr. cab elevation, straight boom 31'6", angled stick 29'6" and multi-tine grab GMM 50-5/1.18 yd³ semi-closed tines.

Weight	118,600 lb
Pad width	24"
Ground pressure	on request

16		15	ft	20	ft	25	ft	30	ft	35	ft	40	ft	45	ft	50	ft	55	ft	-	~ <u>₽</u>	_
12/			4		4		4		4		4		4		4		1		9			ے ا
ft	Undercarriage	-4	25	4		4		-40		− ∰		-47		-43		-47			쁘	₽		ft in
70	SW			13,5*	13,5*															12,6*	12,6*	21' 2"
65	SW					13,6*	13,6*	10,8*	10,8*											9,7*	9,7*	31' 5"
60	SW							13,2*	13,2*	10,9*	10,9*									8,3*	8,3*	38' 5"
55	SW							14,1*	14,1*	12,7*	12,7*	10,5*	10,5*							7,5*	7,5*	43' 8"
50	SW									12,6*	12,6*	11,5*	11,5*	9,7*	9,7*					7,0*	7,0*	47'11"
45	SW									12,5*	12,5*	11,4*	11,4*	10,5*	10,5*	8,2*	8,2*			6,7*	6,7*	51' 4"
40	SW									12,5*	12,5*	11,4*	11,4*	10,5*	10,5*	9,7*	9,7*			6,5*	6,5*	54'
35	SW							14,2*	14,2*	12,7*	12,7*	11,5*	11,5*	10,5*	10,5*	9,7*	9,7*	7,8*	7,8*	6,4*	6,4*	56' 1"
30	SW							14,6*	14,6*	13,0*	13,0*	11,7*	11,7*	10,6*	10,6*	9,7*	9,7*	8,8*	8,8*	6,3*	6,3*	57' 8"
25	SW					17,1*	17,1*	15,2*	15,2*	13,4*	13,4*	11,9*	11,9*	10,8*	10,8*	9,8*	9,8*	8,8*	8,8*	6,3*	6,3*	58'10"
20	SW			18,7*	18,7*	18,7*	18,7*	15,8*	15,8*	13,8*	13,8*	12,2*	12,2*	10,9*	10,9*	9,8*	9,8*	8,8*	8,8*	6,3*	6,3*	59' 6"
15	SW	32,9*	32,9*	24,6*	24,6*	19,7*	19,7*	16,5*	16,5*	14,2*	14,2*	12,4*	12,4*	11,0*	11,0*	9,8*	9,8*	8,7*	8,7*	6,4*	6,4*	59'10"
10	SW	23,6*	23,6*	26,2*	26,2*	20,6*	20,6*	17,1*	17,1*	14,5*	14,5*	12,6*	12,6*	11,1*	11,1*	9,7*	9,7*	8,4*	8,4*	6,6*	6,6*	59' 7"
5	SW	11,1*	11,1*	26,9*	26,9*	21,1*	21,1*	17,3*	17,3*	14,6*	14,6*	12,6*	12,6*	10,9*	10,9*	9,5*	9,5*	8,0*	8,0*	6,1*	6,1*	59' 1"
0	SW	10,0*	10,0*	21,9*	21,9*	21,0*	21,0*	17,2*	17,2*	14,5*	14,5*	12,3*	12,3*	10,6*	10,6*	9,0*	9,0*	7,1*	7,1*	5,7*	5,7*	57' 8"
- 5	SW	10,7*	10,7*	19,2*	19,2*	20,0*	20,0*	16,5*	16,5*	13,8*	13,8*	11,7*	11,7*	9,8*	9,8*	8,0*	8,0*			6,2*	6,2*	54' 2"
-10	SW			19,2*	19,2*	17,9*	17,9*	14,9*	14,9*	12,5*	12,5*	10,4*	10,4*	8,5*	8,5*					7,0*	7,0*	48' 7"
-15	SW							12,4*	12,4*	10,3*	10,3*									10,2*	10,2*	35' 4"

Height Can be slewed through 360° Lin longitudinal position of undercarriage Max. reach *Limited by hydr. capacity

The lift capacities on the stick end without attachment are stated in lb x 1,000 and can be slewed through 360° on a firm, level supporting surface. Capacities are valid for 24" wide flat pads. Indicated loads based on the ISO 10567 standard and do not exceed 75% of tipping or 87% of hydraulic capacity. The lift capacity values indicated are attained at the corresponding operating temperature. This operating temperature is ensured by continuous movement of the

boom. Weights of fitted attachments (grabs, load hooks, etc.) and load accommodation attachment are to be deducted from the lift capacity values. The lift capacity of the unit is limited by its stability, the lifting capability of the hydraulic elements, or the maximum permissible lifting capacity of the load hook.

Liebherr ERC-System


More performance, less consumption

Lowering the equipment stores energy in the ERC-System. This stored energy is then made available to the machine to provide additional engine power. When the equipment is raised the stored energy is released and is reflected in powerful, homogeneous operating cycles. The result is a clear energy saving – and, at the same time, even greater performance.

System performance

The energy recovery cylinder is a storage system which is independent of the electric motor or diesel engine. The system performance of material handling machines fitted with the ERC-System is composed of the installed engine power and the energy recovery cylinder. When the equipment is raised, energy from the ERC-System is supplied in addition to the power from the engine.

ERC-System



System performance
Engine power
ERC performance



B 1. Equipment fitting raised / energy released




2. Lower equipment fitting/store energy

4. Raise equipment fitting / release energy



Equipment fitting lowered/ energy stored



Attachments



Grab for loose material

Grab model GMZ 40											
Shell specification		Standard				Wide					
Width of shells	ft in	3'11"	4'11"	5'9"	6'3"	3'11"	4'11"	5'9"	6'7"	7'5"	8'2"
Capacity	yd ³	2.75	3.27	3.92	4.58	1.57	1.96	2.29	2.62	2.94	3.27
Weight	lb	3,835	4,155	4,420	4,585	3,395	3,670	3,900	4,135	4,520	4,750



Multi-tine grab		open			semi-closed			closed, heart-shaped			
Grab model GM 65 (5 tines)											
Capacity	yd3	0.52	0.78		0.52	0.78		0.52	0.78		
Weight	lb	2,590	2,890		2,975	3,285		3,010	3,540		
Grab model GM 69 (4 tines)											
Capacity	yd3	1.05	1.44		1.05	1.44		1.05	1.44		
Weight	lb	3,065	3,165		3,485	3,735		4,290	4,630		
Grab model GMM 50-5 (5 tines)											
Capacity	yd³	0.92	1.18	1.44	0.92	1.18	1.44	0.92	1.18	1.44	
Weight	lb	3,570	3,880	3,900	3,735	4,070	4,135	3,945	4,300	4,310	



Wood grab

•									
Grab model GMH 40 - round overlapping (vertical cylinders)									
Size	yd ²	1.20	1.55	1.79	2.03	2.27			
Cutting width	ft in	2'8"	2'8"	2'8"	2'8"	2'8"			
Height of grab, closed	ft in	8'5"	8'9"	8'11"	9'3"	9'6"			
Weight	lb	3,470	3,540	3,650	3,660	3,945			



Sorting grab	ribbed	perforated	ribbed	perforated	ribbed	perforated
Grab model SG 30B						
Width of shells	ft in 3'3"	3'3"	3'11"	3'11"	4'7"	4'7"
Capacity	yd ³ 0.98	1.11	1.18	1.31	1.37	1.50
Max. closing force	lbf 17,98	17,985	17,985	17,985	17,985	17,985
Weight incl.						
quick coupler mounting SWA 66	lb 4,145	3,935	4,345	4,070	4,555	4,200



Load hook

Max. load	lb	27,560
Height with suspension	ft in	3'1"
Weight	lb	300



Magnet devices / lifting magnets

Generator	kW	13/20	13/20
Electromagnet with suspension			
Power	kW	8.8	10
Diameter of magnet	ft in	4'1"	4'5"
Weight	lb	2,890*	3,750*

^{*} only magnet plate

Equipment

∞	40 M	20 M	40 C	50 M HR	50 C HR
Support assistant	+	+		+	
Axles with increased traction (reduced speed)		+			
Trailer coupling	+	+			
Track pads, variants			+		+
Individual control outriggers	+	+		•	
Three-piece chain guide			+		•
Shuttle axle lock, automatic	•	•		•	
Outrigger monitoring system	+	+		+	
Tires, variants	+	+		+	
Trailing cable ²⁾	•		•		
Protection for piston rods, outriggers	+	+		+	
Two storage compartments ¹⁾	•	•			
One storage compartment ²⁾	•				
Cable reel system ²⁾	+				

Uppercarriage	40 M	20 M	70 C	50 M HR	50 C HR
Uppercarriage right side light, 1 piece, LED	•	•	•	•	•
Uppercarriage rear light, 2 pieces, LED	+	+	+		
Uppercarriage underneath rear light, 1 piece, LED				+	+
Tank refilling pump fuel ¹⁾	+	+	+	+	+
Railing on uppercarriage	+	+	+	•	•
Generator	+	+	+	+	+
Main battery switch for electrical system	•	•	•	•	•
Amber beacon, at uppercarriage, LED double flash	+	+	+	+	+
Protection for headlights	+	+	+		
Protection for rear lights	+	+	+		
Tool equipment, extended	•	•	•	•	•

Hydraulic system	40 M	20 M	70 C	50 M HR	50 C HR
Electronic pump regulation	•	•	•	•	•
Liebherr hydraulic oil from -4°F to +104°F	•	•	•	•	•
Liebherr hydraulic oil, biologically degradable	+	+	+	+	+
Liebherr hydraulic oil, specially for warm or cold regions	+	+	+	+	+
Magnetic rod in hydraulic tank	•	•	•	•	•
Bypass filter	+	+	+	+	+
Preheating hydraulic oil	+	+	+	+	+

Engine	40 M	20 M	40 C	50 M HR	50 C HR
Fuel anti-theft device ¹⁾	+	+	+	+	+
Air pre-filter with dust discharge ¹⁾	+	+	+	+	+
Automatic engine shut-down (time adjustable)	+	+	+	+	+
Preheating fuel ¹⁾	+	+	+	+	+
Preheating coolant ¹⁾	+	+	+	+	+
Preheating engine oil*1)	+	+	+	+	+

≈ J Cooling system	40 M	20 M	40 C	50 M HR	50 C HR
Reversible fan drive	+	+	+	+	+
Protective grid in front of cooler intake	•	•	•	•	•

	I		ı	또	~
Cab	Σ	Σ	၁	Σ	CHR
	9	20	40	20	20
Stabilizer, control lever, left console	+	+		+	
Stabilizer, proportional control on left joystick	•	•		•	
Cab lights rear, halogen	+	+	+	+	+
Cab lights rear, LED	+	+	+	+	+
Cab lights front, halogen	+	+	+	+	+
Cab lights front, halogen (under rain cover)	•	•	•	•	•
Cab lights front, LED	+	+	+	+	+
Cab lights front, LED (under rain cover)	+	+	+	+	+
Armrest adjustable	•	•	•	•	•
Circular bubble level	+	+	+	•	•
Slewing gear brake Comfort, button on the left or right joystick	+	+	+	+	+
Driver profile, personalized (max. 5 drivers)	+	+	+	+	+
Operator's seat Comfort	•	•	•	•	•
Operator's seat Premium	+	+	+	+	+
Driving alarm (acoustic signal is emitted during travel, can be					
switched ON/OFF)	+	+	+	+	+
Fire extinguisher	+	+	+	+	+
Footrest	+	+	+	+	+
Horn, button on left joystick	•	•	•	•	•
Joystick steering (max. 7.5 mph)	•	•		•	
Joystick and wheel steering (slim version)	+	+		+	
Cab elevation, hydraulic (LHC)	•	•	•	•	•
Cab elevation, hydraulic with tilt function (LHC)	+	+	+		
Cab elevation, rigid (LFC)	+	+	+		
Automatic air conditioning	•	•	•	•	•
Wheel steering (slim version)	+	+		+	
LiDAT, vehicle fleet management	•	•	•	•	•
Engine shut-down (emergency stop) cab ²⁾	•		•		
Proportional control	•	•	•	•	•
Radio Comfort, control via display with handsfree set	+	+	+	+	+
Preparation for radio installation	•	•	•	•	•
Back-up alarm (acoustic signal is emitted traveling backward,					
can not be switched off)	+	+		+	
Amber beacon, on cab, LED double flash	+	+	+	+	+
Windows made from impact-resistant laminated safety glass	+	+	+	•	•
Windscreen wiper, roof	+	+	+	+	+
Windshield wiper, entire windshield	•	•	•	•	•
FOPS top guard	+	+	+	+	+
FGPS front guard, tiltable	+	+	+	+	+
Sun visor	+	+	+	+	+
Stationary air-conditioning ²⁾	•		•		
Left control console, folding	•	•	•	•	•

Equipment	40 M	50 M	40 C	50 M HR	50 C HR
Boom lights, 2 pieces, halogen	•	•	•	•	•
Boom lights, 2 pieces, Hategeri	+	+	+	+	+
Stick lights, 2 pieces, halogen	•	•	•	•	•
Stick lights, 2 pieces, LED	+	+	+	+	+
Boom shutoff (retract / extend), electronically	+	+	+	+	+
Equipment with electro-hydraulic end position control	•	•	•	•	•
AutoLift	+	+	+	+	+
Pressure warning mechanism hoist cylinder	•	•	•	•	•
ERC system	•	•	•	•	•
Filter system for attachment	+	+	+	+	+
Electronic lift limitation	+	+	+	+	+
Boom cylinder cushioning	•	•	•	•	•
Stick camera (with separate monitor), bottom side, with protection	+	+	+	+	+
Load torque limitation	+	+	+	+	+
Liebherr multi coupling system	+	+	+	+	+
Liebherr quick coupler, hydraulic	+	+	+		
Pipe fracture safety valves hoist cylinders	•	•	•	•	•
Pipe fracture safety valves stick cylinders	•	•	•	•	•
Quick coupling system Solidlink	+	+	+		
Quick coupling system MH 40B	+	+	+	+	+
Protection for piston rod, energy recovering cylinder	+	+	+	+	+
Protection for piston rods, hoist cylinder	+	+	+	+	+
Protection for piston rods, stick cylinder	+	+	+		
Stick shutoff (retract), electronically	•	•	•	•	•
Stick shutoff (retract / extend), electronically	+	+	+	+	+
Retract stick without pressure	•	•	•	•	•
Sticks with quick coupling	+	+	+	+	+
Overload warning device	+	+	+	+	+

Complete machine	40 M	20 M	40 C	50 M HR	50 C HR
Lubrication					
Lubrication undercarriage, manually – decentralized (grease points)	•	•			
Lubrication undercarriage, manually - centralized (one grease point)	+	+		•	
Central lubrication system for uppercarriage and equipment, automatically	•	•	•	•	•
Central lubrication system for undercarriage, automatically	+	+		+	
Centralized lubrication extended for attachment	+	+	+	+	+
Special coating					
Special coating, variants	+	+	+	+	+
Monitoring					
Rear view monitoring with camera	•	•	•	•	•
Side view monitoring with camera	•	•	•	•	•

Options and/or special equipment, supplied by vendors other than Liebherr, are only to be installed with the knowledge and approval of Liebherr in order to retain warranty.

^{• =} Standard, + = Option
* = country-dependent, ¹⁾ not with electric drive, ²⁾ only with electric drive

All illustrations and data may differ from standard equipment. Subject to change without notice. RG-BK \cdot LHB/PMKT-12252044-web-04.24_enUS

The Liebherr Group



Global and independent: more than 70 years of success

Liebherr was founded in 1949. With the development of the world's first mobile tower crane, Hans Liebherr laid the foundations of a successful family business which today comprises more than 140 companies on all continent and employs nearly 51,000 people. The parent company of the Group is Liebherr-International AG in Bulle (Switzerland), whose associates are exclusively members of the Liebherr family.

Technology leadership and pioneering spirit

Liebherr regards itself as a pioneer. This spirit has enabled the company to make a decisive contribution to the technological history of many industries. Today, employees around the world still share the courage of the company founder to take new paths. They are all united by a passion for technology and fascinating products and the determination to perform outstanding work for their customers.

Widely diversified product portfolio

Not only is Liebherr one of the biggest construction equipment manufacturers in the world, it also provides high-quality, user-oriented products and services in a wide range of other areas. The product portfolio includes the segments earthmoving, material handling technology, deep foundation machines, mining, mobile and crawler cranes, tower cranes, concrete technology, maritime cranes, aerospace and transportation systems, gear technology and automation systems, refrigeration and freezing, components and hotels.

Customized solutions and maximum customer benefit

Liebherr solutions are characterized by maximum precision, outstanding implementation and exceptional longevity. Its mastery of key technologies enables the company to offer its customers customized solutions. For Liebherr, customer focus does not end with the product; it also encompasses a wide range of services that make a real difference.

www.liebherr.us



Breathing diesel engine exhaust exposes you to chemicals known to the State of California to cause cancer and birth defects or other reproductive harm.

- Always start and operate the engine in a well-ventilated area.
- If in an enclosed area, vent the exhaust to the outside.
- Do not modify or tamper with exhaust system.
- Do not idle the engine except as necessary.
- For more information go to www.P65warnings.ca.gov/diesel.



This product can expose you to chemicals including lead and lead compounds, which are known to the State of California to cause cancer and birth defects or other reproductive harm.

For more information go to www.P65warnings.ca.gov.

Liebherr USA, Co.

Construction Equipment Division • 4800 Chestnut Avenue • Newport News, VA 23607, USA • Phone +1 (757) 240 4250 construction.usa@liebherr.com • www.liebherr.us • www.facebook.com/LiebherrConstruction